



Powering Business Worldwide

USB / FireWire® - USB 1.1 Cable (iMac Blue) - 6 ft.

MODEL NUMBER: **U002-006-IB-R**

Description

Tripp Lite's 6-ft. USB A/B device cable is designed to connect a USB device to the USB port on a computer or USB hub. This high quality cable delivers the performance and reliability you expect from a USB cable. The cable features gold plated copper contacts for superior conductivity. It is manufactured with molded connectors which include integral strain relief to ensure durability. Double shielding provides maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Features

- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/20 AWG data lines
- Gold plated contacts provide superior conductivity
- Molded connectors which include integral strain relief to ensure durability
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Highlights

- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/20 AWG data lines
- Gold plated connectors provide superior conductivity for low and high speed devices (1.5 to 12 Mbps.)
- Retail packaging

Package Includes

- 6-ft. USB AB Cable USB-A to USB-B, Blue

Specifications

OVERVIEW	
UPC Code	037332014634
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB B (MALE)
PHYSICAL	
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	6.75 x 5.75 x 1.25
Shipping Dimensions (hwd / cm)	17.14 x 14.60 x 3.18
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.