

## 6-ft. USB A/A Extension Cable (A Female to Adjustable Right Angle A Male Connector)

MODEL NUMBER: U014-006



### Highlights

- Adjustable "A" Male connector allows for multiple exit configurations
- Premium double-shielded USB 2.0 cable with tinned copper braid and aluminum mylar foil feature twisted data lines
- Gold plated contacts provide superior conductivity for low and high speed devices

### System Requirements

- USB port and device

### Package Includes

- 6ft USB A/A Cable w/Adjustable Angle A Male Connector

### Description

Tripp Lite's 6-ft. Adjustable "A" Male connector USB A/A extension cable is designed to extend the length of an existing USB cable. Adjustable angle connector allows the cable to exit at any angle...perfect where space is limited. This high quality cable delivers the performance and reliability you expect from a USB cable. The cable features gold plated contacts for superior conductivity. It is manufactured with molded connectors which include integral strain relief to ensure durability. Double shielding provides maximum EMI/RFI protection. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Two elbow joints allow for Up-Down-Left-Right exit configurations where space constraints are an issue
- Premium double-shielded USB 2.0 cable with tinned copper braid and aluminum Mylar foil feature twisted data lines
- Gold plated copper contacts provide superior conductivity
- Molded connectors which include integral strain relief to ensure durability
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332122001
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
PHYSICAL	



Powering Business Worldwide

TRIPP LITE  
SERIES

Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.25 x 6.75 x 0.50
Shipping Dimensions (hwd / cm)	23.50 x 17.14 x 1.27
Shipping Weight (lbs.)	0.21
Shipping Weight (kg)	0.10
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.