

USB 2.0 A to Mini-B Coiled Cable (M/M), 3 ft. (0.91 m)

MODEL NUMBER: **U030-003-COIL**



Connects high-speed USB 2.0 mobile devices with a USB Mini-B port to your computer, laptop or other compatible USB-A device. Ideal for digital cameras, MP3 players and smartphones with a 5-pin port.

Description

The U030-003-COIL USB 2.0 Hi-Speed A to Mini-B Coiled Cable (M/M) connects your computer, laptop or other compatible USB-A device to a USB Mini-B mobile device. Ideal for digital cameras, MP3 players and smartphones with a 5-pin port, this 3-ft. (0.91 m) cable supports data transfer rates up to 480 Mbps for both low- and high-speed devices, including multimedia applications.

The specially coiled cable takes up much less space than a regular 3-ft. (0.91 m) cable. It also resists tangles and knots, making it convenient to store in your car or carry in your purse, backpack or laptop bag.

Molded nickel-plated connectors ensure excellent conductivity. Integral strain relief ensures the cable and connectors last a long time. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

Features

Connect and Power Your Mobile Devices

- Ideal for digital cameras, MP3 players and smartphones with a 5-pin port
- Supports data transfer rates up to 480 Mbps
- Backward compatible with earlier USB generations

Coiled to Take Up Less Space than Regular 3-ft. (0.91 m) Cable

- Resists tangles and knots
- Stores perfectly in car, purse, backpack or laptop bag

First-Rate Construction for Superior Signal Transfer

- Molded nickel-plated connectors for optimal signal quality

Highlights

- Supports data transfer rates up to 480 Mbps
- Molded nickel-plated connectors
- Twisted 28/24 AWG data/power lines
- 3-ft. (0.91 m) cable is coiled to take up less space

System Requirements

- Device requiring USB cable with Mini-B 5-pin connector
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

Package Includes

- U030-003-COIL USB 2.0 Hi-Speed A to Mini-B Coiled Cable (M/M), 3-ft. (0.91 m)



Powering Business Worldwide

TRIPP LITE
SERIES

- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332197214
Technology	USB 2.0 (High Speed)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB MINI-B 5-PIN (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.75
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.76
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.