

USB 3.0 2-Port Panel Mount Adapter, 20-Pin Motherboard IDC to 2x USB-A Female, 18 in.

MODEL NUMBER: U321-18N-20P-PM



Highlights

- Supports data transfer speeds up to 5 Gbps
- 20-pin IDC plug connects to computer's motherboard
- Dual USB-A ports attach to front panel with included screws
- Corrosion-resistant gold-plated connectors
- Backward compatible with previous USB generations

Package Includes

- U321-18N-20P-PM USB 3.0 2-Port Panel Mount Adapter, 18 in.

Adds two front-panel USB 3.0 ports to your computer via the motherboard's 20-pin connector.

Description

The U321-18N-20P-PM USB 3.0 2-Port Panel Mount Adapter adds two USB 3.0 ports to your computer. Consistent with current industry standards, this 18-inch cable attaches to your PC's motherboard with a 20-pin IDC plug. The cable's USB-A ports support USB 3.0 data transfer speeds up to 5 Gbps—perfect for sharing video, music, images and other large files. The dual USB-A ports attach to the computer's front panel using the included screws. Gold-plated connectors resist corrosion and ensure optimal signal transfer. Molded construction with strain relief guarantees durability and long life. Flexible PVC jacket makes the blue cable easy to install in tight spaces. Backward compatible with previous USB generations.

Features

Adds USB 3.0 Capability to Your PC

- Dual USB-A ports attach to your computer's front panel with included screws
- 20-pin IDC connector attaches to computer's motherboard
- Supports data transfer speeds up to 5 Gbps
- Backward compatible with previous USB generations

Premium Construction for Premium Performance

- Corrosion-resistant gold-plated connectors for optimal signal transfer
- Fully molded construction with strain relief for durability and long life
- Flexible PVC jacket easy to install in tight spaces
- Conforms to industry standards

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332191397
CONNECTIONS	
Side A - Connector 1	4 PIN (INTERNAL)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
PHYSICAL	
Color	Blue
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Cable Length (in.)	18
Cable Length (cm)	45.72
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.