

USB 3.1 Gen 1 (5 Gbps) to CFast 2.0 Card and SATA III Adapter, USB-A

MODEL NUMBER: U338-CF-SATA-5G



Connects a CFast 2.0 memory card and/or SATA drive to your computer, laptop, netbook, tablet or hub's USB-A port.

Features

Quickly Downloads Photos and Videos from a CFast 2.0 Card to Your Laptop's USB Port This card reader and adapter provides a fast and simple way to download photos and videos from a CFast memory card to a computer. Ideal for photographers and videographers, this unit connects to your computer, laptop, netbook, tablet or hub's USB port via its built-in cable. Just insert your CFast 1.0 or 2.0 memory card into the unit's slot to transfer high-resolution image and video files in a hurry. A blue LED indicates when the CFast card is ready for reading or writing.

Also Connects a 2.5 in. SATA Drive to Your Computer, Laptop, Netbook, Tablet or Hub This unit is also recommended for backing up important data, retrieving old data and storing new data without the time, trouble and expense of installing a SATA drive inside your computer. Just connect a 2.5-inch SATA III, II or I hard disc drive (HDD) or solid state drive (SSD) up to 2 TB to the adapter, which allows you to download data to your computer or use the SATA drive as extra storage space. A red LED indicates when the SATA drive is ready for reading or writing. The SATA drive and CFast memory card can both be used at the same time.

Transfers Data at Fast USB 3.1 Gen 1 Speeds The adapter supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. It's backward compatible with previous USB generations, allowing you to use it with older equipment. It also reads data up to 70 percent faster and writes up to 40 percent faster when connected to a UASP-enabled host controller.

It's Plug-and-Play, So You Can Begin Transferring Important Files Right Away No software, drivers or external power is needed. The adapter works with all major operating systems, including Windows, Mac and Linux. The portable unit is about the size of a credit card, so you can easily take it with you in a backpack, briefcase, laptop bag or even your pocket.

Highlights

- Ideal for photographers and videographers who need to upload large files quickly
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Compatible with 2.5 in. SATA I, II and III HDDs and SSDs up to 2 TB
- Works with all major operating systems, including Windows, Mac and Linux
- Easy installation with plug-and-play operation—no software or drivers required

Applications

- Transfer high-definition video and image files between a digital camera or camcorder and your computer or laptop
- Load a file onto a SATA drive or CFast memory card at the office for presenting on a different computer elsewhere
- Temporarily store data that cannot be emailed to another computer or uploaded to cloud storage

System Requirements

- Device with a USB-A port (USB 3.1 Gen 1 compatibility required to achieve USB 3.1 Gen 1 speeds)
- CFast memory card
- 2.5 in. SATA HDD or SSD up to 2 TB
- Any major operating system that complies with USB standards

Package Includes

- U338-CF-SATA-5G USB 3.1 Gen 1 (5 Gbps) to CFast 2.0 Card and SATA III Adapter, USB-A
- Owner's manual

Specifications

OVERVIEW	
UPC Code	03733222091



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	SATA/eSATA
AUDIO	
Audio Specification	No
INPUT	
Built-In Cable Length (ft.)	0.39
Built-In Cable Length (m)	0.12
Built-In Cable Length (in.)	4.72
Built-In Cable Length (cm)	12
Bus Powered	Yes
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE); CF (Male)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue (CFast Card connection), Red (SATA connection), Blue/Red (CFast/SATA connection)
PHYSICAL	
Color	Black
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.12 x 3.60 x 4.40
Shipping Dimensions (hwd / cm)	2.86 x 9.14 x 11.18
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
Unit Dimensions (hwd / in.)	2.500 x 1.500 x 0.600
Unit Dimensions (hwd / cm)	6.4 x 3.7 x 1.5
Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03
ENVIRONMENTAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Operating Temperature Range	32° to 167°F (0° to 75°C)
Storage Temperature Range	14° to 176°F (-10° to 80°C)
Relative Humidity	0-80% non-condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
IP68 Rated	No
IP20 Rated	No
UASP Support	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.