

# USB-C to USB-B Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U422-003-G2**



Connects a computer, laptop, tablet, smartphone or other device with a USB-C port to a device or peripheral with a Type-B port, such as a hub or external hard drive.

## Features

**Supports USB 3.2 Gen 2** Recommended for smartphones, tablets, laptops, computers, external hard drives, hubs and other compatible devices Data transfer speeds up to 10 Gbps—20 times faster than USB 2.0  
**USB-B male connector** Backward compatible with previous USB generations

**USB-C Male Connector** Fumble-free reversible plug ensures fast, easy connection every time

**Premium Construction for Superior Signal Transfer** Foil and braid shielding for error-free signal quality and EMI/RFI protection Molded nickel-plated connectors and gold-plated contacts Integral strain relief for long life Rugged PVC jacket

## Highlights

- USB 3.2 Gen 2 data transfer speeds up to 10 Gbps
- Reversible USB-C male connector for fast connection the first time
- Error-free signal quality and EMI/RFI protection
- Backward compatible with previous USB generations

## System Requirements

- Device with a USB-C port
- Device with a USB Type-B port

## Package Includes

- U422-003-G2 USB 3.2 Gen 2 (10 Gbps) Cable, USB-C to USB Type-B (M/M), 3 ft.

## Specifications

OVERVIEW	
UPC Code	037332197375
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight



Powering Business Worldwide

TRIPP LITE  
SERIES

PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 6.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 15.24 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10 to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.