

USB-C Multiport Adapter, USB 3.x (5Gbps), USB-A/C Hub Ports, Card Reader, Silver

MODEL NUMBER: U460-002-2AM-C1



Adds USB-A and USB-C ports and memory card slots to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, tablet or notebook.

Features

USB-C/Thunderbolt 3 Hub Connects USB Peripherals to Your Laptop or TabletThis USB-C hub allows you to connect up to three USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. This lets you expand the potential of your device by connecting USB peripherals, such as an external hard drives, flash drives, power meters and printers.

USB Ports Transfer Data from Peripheral to Device at Fast USB 3.1 Gen 1 SpeedsBoth USB-A ports and the USB-C port transfers data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.**Note:** Host must support USB OTG (On-the-Go)**Dual Memory Card Slots Are Ideal for Moving Large Files**

You can also insert memory cards into their corresponding slots to transfer data at USB 2.0 speeds up to 480 Mbps. The memory card readers support MicroSD and SD/MMC cards for convenient access to digital photos, camcorder videos, smartphone data and other essential files. Both memory card slots can be used simultaneously for maximum access to external storage.

Built-In USB-C Cable Connects in Either DirectionConnect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the PackageThe plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. The aluminum housing is about the size of a credit card to make it easy to carry in a pocket, backpack or laptop bag for use anywhere.

Specifications

OVERVIEW	
UPC Code	037332218353

Highlights

- USB-C 3.1 hub is compatible with all USB-C and Thunderbolt 3 devices
- Connects external hard drives, keyboard, printer and other USB peripherals
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 3 USB peripherals, such as an external hard drive, flash drive and keyboard/mouse
- Transfer photos, videos and other important files between your MacBook or Chromebook and a memory card

System Requirements

- Device with USB-C or Thunderbolt 3 port (USB 3.1 port needed to achieve USB 3.1 speeds)

Package Includes

- U460-002-2AM-C1 USB 3.1 Gen 1 USB-C Portable Hub/Adapter
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Multiport Adapter
Technology	USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	1
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(2) USB A (FEMALE); USB C (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 1 (5 Gbps); USB-C - USB 3.2 Gen 1 (5 Gbps)
STORAGE	
Card Slots	SD (FEMALE); MICRO SD (FEMALE)
Card Slots Details	SD 3.0 Memory Card slots (SD and MicroSD) - both can be used simultaneously
INPUT	
Built-In Cable Length (ft.)	0.492
Built-In Cable Length (in.)	5.91
Built-In Cable Length (cm)	15
Bus Powered	Yes
Product Length (in.)	4.49
Product Length (cm.)	11.35
Product Length (ft.)	0.372
Product Length (m)	0.113
BATTERY	
Battery Charging (5V/1.5A Port)	No
CONNECTIONS	
Number of Ports	5
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	MICRO SD (FEMALE)
Side B - Connector 3	SD (FEMALE)
Side B - Connector 4	USB C (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Connection)
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	4.5 +/- 0.15 mm
Wire Gauge (AWG)	24/30
Housing Color	Silver
Unit Dimensions (hwd / in.)	0.530 x 1.310 x 4.470
Unit Packaging Type	Box
Unit Weight (lbs.)	0.154
Unit Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-14° to 140°F (-10° to 60°C)
Relative Humidity	0-90% non-condensing
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
SD Card Specification	Micro SD; SD
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.