

## Universal Reversible USB 2.0 Super Slim Cable (Reversible A to B M/M), 6 ft.

MODEL NUMBER: UR022-006-SLIM



### Highlights

- Super Slim design...over 35% thinner than standard USB A/B device cables
- Universal, Reversible "A" connector allows plugging in any direction
- Supports USB 2.0 data transfer rates up to 480Mbps

### System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with a USB 2.0 device and USB 2.0 controller

### Package Includes

- Universal Reversible USB 2.0 A-Male to B-Male Super Slim Device Cable - 6ft

### Description

Tripp Lite's UR022-006-SLIM, 6-ft. USB 2.0 A/B device cable features a Super Slim design that is more than 35% thinner than standard USB 2.0 A/B device cables. It also includes a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. It supports USB 2.0 data transfer rates up to 480Mbps, and is backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

### Features

- Super Slim design...over 35% thinner than standard USB A/B device cables
- Universal, Reversible "A" connector allows plugging in any direction
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair, 30AWG Power pair

## Specifications

OVERVIEW	
UPC Code	037332188137
Technology	USB 2.0 (High Speed)
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE  
SERIES

Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
<b>PHYSICAL</b>	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.11
Shipping Weight (kg)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-10 to 75° C (14 to 167° F)
Storage Temperature Range	-20 to 80° C (-4 to 176° F)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.