

Universal Reversible USB 2.0 Cable (Up / Down Angle Reversible A to B M/M), 6-ft.

MODEL NUMBER: UR022-006-UDA



Highlights

- 6-ft., USB 2.0, A/B Peripheral device cable
- Universal, Up / Down Angle Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB 2.0 performance only when used with USB 2.0 device and USB 2.0 controller

Package Includes

- Up / Down Angle Reversible USB 2.0 A-Male to B-Male Device Cable - 6ft

Up / Down Angle Reversible USB "A" connector plugs in any direction

Description

Tripp Lite's UR022-006-UDA, 6-ft. USB2.0 A/B device cable, with Up / Down Angle Reversible "A" connector, meets or exceeds USB 2.0 specifications. No guessing on how to plug into the Computer or Hub port...Connects in either direction! Backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- 6-ft., USB 2.0 A-Male to B-Male, with Up / Down Angle Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332185297
Technology	USB 2.0 (High Speed)
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.