

Universal Reversible USB 2.0 Cable (Reversible A to B M/M), White, 6 ft. (1.83 m)

MODEL NUMBER: UR022-006-WH



Reversible USB "A" connector plugs in any direction

Features

- 6ft, White, USB 2.0 A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332182043
Technology	USB 2.0 (High Speed)
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB B (MALE)
PHYSICAL	
Color	White
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	0.25 x 5.50 x 8.50

Highlights

- 6-ft. (1.83 m), White, USB 2.0, A/B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- Universal Reversible USB 2.0 A-Male to B-Male Device Cable - White - 6-ft. (1.83 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	0.64 x 13.97 x 21.59
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.