

# Universal Reversible USB 2.0 Cable (Reversible A to Right-angle 5Pin Micro B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR050-006-RAB



Universal / Reversible "A" connector allows plugging in any direction

## Features

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Right-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Available in lengths up to 10-ft.
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

## Specifications

| OVERVIEW                        |                         |
|---------------------------------|-------------------------|
| UPC Code                        | 037332182487            |
| Technology                      | USB 2.0 (High Speed)    |
| CONNECTIONS                     |                         |
| Side A - Connector 1            | REVERSIBLE USB A (MALE) |
| Side B - Connector 1            | MICRO-USB B (MALE)      |
| PHYSICAL                        |                         |
| Color                           | Black                   |
| Cable Length (ft.)              | 6                       |
| Cable Length (m)                | 1.83                    |
| Shipping Dimensions (hwd / in.) | 0.25 x 5.00 x 7.10      |

## Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Right-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates

## System Requirements

- Digital devices that use the USB Micro-B Female socket

## Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Right-Angle Micro-USB B Device Cable (A Male to Micro-B Male)



Powering Business Worldwide



|                                     |                           |
|-------------------------------------|---------------------------|
| Shipping Dimensions (hwd / cm)      | 0.64 x 12.70 x 18.03      |
| Shipping Weight (lbs.)              | 0.10                      |
| Shipping Weight (kg)                | 0.05                      |
| <b>ENVIRONMENTAL</b>                |                           |
| Operating Temperature Range         | -10/+75° C                |
| Storage Temperature Range           | -20/+80° C                |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.