



Tripp Lite Domestic Parallel Tie Cabinet with Bypass Panel


Model #	Compatible UPS System	Ship Dimensions (HWD)(in)	Shipping (lb)	Unit Dimensions (in)					Unit Weight (lb)	Design Voltage	Breaker Amps		Breaker KAIC	Kirk Key
				A	B	C	D	E			Bypass	Each UPS		
SUPC2MBP40K	SU40K	62 x 38.9 x 12.5	375	36.12	11.75	61.25	32	57.12	370	208	300	150	65	Yes
SUPC2MBP60K	SU60K	70.25 x 38.9 x 12.5	490	38.12	11.75	69.5	34	65.37	485	208	450	225	65	Yes
SUPC2MBP60KTV	SU60KTV	43.13 x 30.88 x 12.5	225	30.12	11.75	42.37	26	38.25	220	480	200	100	35	Yes
SUPC2MBP80K	SU80K	70.25 x 38.9 x 12.5	490	38.12	11.75	69.5	34	65.37	485	208	600	300	65	Yes
SUPC2MBP80KTV	SU80KTV	43.13 x 30.88 x 12.5	225	30.12	11.75	42.37	26	38.25	220	480	225	125	35	Yes



LEFT SIDE VIEW




FRONT VIEW



FRONT VIEW (DOOR REMOVED)

SEQUENCE OF OPERATION STICKER DETAIL



PANEL TYPE: CDP (UL 67 LISTED INTERIOR)

SERVICE: SEE TABLE ABOVE.

ALTERNATE VOLTAGES: 208V, 380/400/415V.

ALTERNATE VOLTAGE STICKERS: PROVIDE STICKERS WITH ALTERNATE VOLTAGES TO BE APPLIED IN FIELD AS REQUIRED. STICKERS INCLUDED IN BAG WITH KEYS.

ENCLOSURE: NEMA 1 (UL 50 LISTED ENCLOSURE)

BOX: 12 GAUGE PAINTED STEEL, NO KNOCKOUTS.

TRIM: 12 GAUGE PAINTED STEEL, HELD TO BOX WITH ADJUSTABLE TRIM CLAMPS—SURFACE MOUNTING.

DOOR: EQUIPPED WITH SIERRA GE1RH1 SNAPLOCK.

FINISH: GRAY POLYESTER POWDERCOAT APPLIED TO SURFACES TREATED WITH AN IRON PHOSPHATE AND CHROME FREE SEALER.

BUS: ELECTROLYTIC COPPER OF 98% CONDUCTIVITY, BASED ON 1000 AMPS PER SQUARE INCH DENSITY.

WIRE BENDING GUTTER: MEETS OR EXCEEDS NEC TABLES 312-6(a), 312-6(b).

BREAKERS: CUTLER-HAMMER THERMAL-MAGNETIC, 3 POLE, AS INDICATED: SEE TABLE ABOVE FOR BREAKER TYPE, AMPS.

BREAKER TERMINAL LUG: (2) 2/0-250MCM OR (1) 2/0-500MCM PER PHASE.

KEY INTERLOCK: KIRK TYPE F, CBSSB LOCKED IN THE OPEN POSITION, CBOL LOCKED IN THE CLOSED POSITION.



**For more information, call
Tripp Lite Customer Service at
(773) 869-1234.**

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from actual product.