



S3M25K-30K4T Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)									
			2.5kW	5kW	7.5kW	10kW	12.5kW	15kW	17.5kW	20kW	22.5kW	25kW
S3M25K-30K4T	BP240V40	1	181	79	48	33	25	20	16	13	12	10
S3M25K-30K4T	BP240V40	2	397	183	113	80	60	48	40	34	29	25
S3M25K-30K4T	BP240V40	3	615	291	183	130	100	80	66	56	49	43
S3M25K-30K4T	BP240V40L	1	397	183	113	80	60	48	40	34	29	25
S3M25K-30K4T	BP240V40L	2	831	400	255	183	141	114	95	80	70	61
S3M25K-30K4T	BP240V40L	3	1,254	619	401	291	226	184	154	131	114	101
S3M25K-30K4T	BP240V65	1	316	143	88	62	47	37	30	26	22	19
S3M25K-30K4T	BP240V65	2	669	318	201	143	110	88	73	62	54	47
S3M25K-30K4T	BP240V65	3	1,018	496	319	230	178	144	120	102	89	78
S3M25K-30K4T	BP240V65L	1	669	318	201	143	110	88	73	62	54	47
S3M25K-30K4T	BP240V65L	2	1,358	673	437	319	248	202	169	145	126	111
S3M25K-30K4T	BP240V100	1	506	236	148	105	80	64	53	45	38	34

All runtime values are shown in minutes.