



S3M30K-30K4T Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)									
			3kW	6kW	9kW	12kW	15kW	18kW	21kW	24kW	27kW	30kW
S3M30K-30K4T	BP240V40	1	147	63	38	26	20	15	13	11	9.0	7.7
S3M30K-30K4T	BP240V40	2	325	147	91	64	48	38	31	27	23	20
S3M30K-30K4T	BP240V40	3	507	236	148	105	80	64	53	45	38	34
S3M30K-30K4T	BP240V40L	1	325	147	91	64	48	38	31	27	23	20
S3M30K-30K4T	BP240V40L	2	688	327	207	148	113	91	76	64	55	49
S3M30K-30K4T	BP240V40L	3	1,046	510	328	237	183	148	124	106	92	81
S3M30K-30K4T	BP240V65	1	258	115	70	49	37	29	24	20	17	15
S3M30K-30K4T	BP240V65	2	553	259	162	115	88	71	58	49	43	37
S3M30K-30K4T	BP240V65	3	846	407	259	187	144	116	96	82	71	62
S3M30K-30K4T	BP240V65L	1	553	259	162	115	88	71	58	49	43	37
S3M30K-30K4T	BP240V65L	2	1,134	555	358	260	201	163	136	116	101	89
S3M30K-30K4T	BP240V100	1	416	192	119	84	64	51	42	35	30	27

All runtime values are shown in minutes.