



## S3M60KXD Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2.5kW	5kW	7.5kW	10kW	12.5kW	15kW	20kW	25kW	30kW	35kW	40kW	45kW	50kW	54kW
S3M60KXD	BP480V40	1	341	166	105	75	57	45	32	24	19	15	13	11	9.5	8.5
S3M60KXD	BP480V40	2	719	365	237	172	133	107	76	58	46	38	32	28	24	22
S3M60KXD	BP480V40	3	1,091	566	374	274	214	174	125	96	77	63	54	46	41	37
S3M60KXD	BP480V40	4	1,453	767	511	378	297	243	175	135	109	90	77	66	58	53
S3M60KXD	BP480V40	5	1,806	965	648	482	381	313	227	176	142	119	101	88	77	70
S3M60KXD	BP480V40	6	2,149	1,160	784	586	465	383	279	217	176	147	126	109	96	88
S3M60KXD	BP480V200	1	483	239	153	110	85	68	48	36	29	23	20	17	15	13
S3M60KXD	BP480V200	2	998	516	339	248	194	157	112	86	69	57	48	41	36	33
S3M60KXD	BP480V200	3	1,497	792	528	391	308	252	182	140	113	94	80	69	61	55
S3M60KXD	BP480V200	4	1,978	1,063	716	534	423	348	253	197	159	133	113	98	87	79
S3M60KXD	BP480V200	5	2,442	1,329	902	677	538	444	325	254	207	173	148	129	114	104
S3M60KXD	BP480V200	6	2,889	1,590	1,086	818	653	540	398	312	255	214	183	160	141	129
S3M60KXD	BP480V65	1	578	289	186	135	104	83	59	45	35	29	24	21	18	17
S3M60KXD	BP480V65	2	1,182	617	408	300	235	191	137	105	85	70	59	51	45	41
S3M60KXD	BP480V65	3	1,762	940	631	469	370	304	221	171	138	115	98	85	75	68
S3M60KXD	BP480V65	4	2,317	1,257	852	638	507	418	306	238	194	162	138	120	106	97
S3M60KXD	BP480V65	5	2,849	1,567	1,069	806	642	532	392	307	250	210	180	157	139	127
S3M60KXD	BP480V65	6	3,358	1,870	1,284	972	777	645	478	376	308	259	223	194	172	157
S3M60KXD	BP480V300	1	700	355	230	167	129	104	74	56	45	37	31	27	23	21
S3M60KXD	BP480V300	2	1,417	747	497	368	289	236	170	131	106	88	74	64	56	51
S3M60KXD	BP480V300	3	2,098	1,131	764	571	452	372	272	211	171	143	122	106	93	85
S3M60KXD	BP480V300	4	2,744	1,506	1,026	772	615	509	374	293	239	200	172	150	132	121
S3M60KXD	BP480V300	5	3,358	1,870	1,284	972	777	645	478	376	308	259	223	194	172	157
S3M60KXD	BP480V300	6	3,941	2,224	1,537	1,168	938	781	581	459	377	318	274	240	213	195
S3M60KXD	BP480V100	1	906	466	305	223	173	140	100	76	61	50	43	37	32	29
S3M60KXD	BP480V100	2	1,806	965	648	482	381	313	227	176	142	119	101	88	77	70
S3M60KXD	BP480V100	3	2,647	1,449	986	741	590	488	359	280	228	192	164	143	126	115
S3M60KXD	BP480V100	4	3,434	1,916	1,317	997	798	663	491	386	316	266	229	200	177	162
S3M60KXD	BP480V100	5	4,172	2,366	1,640	1,248	1,004	836	623	493	405	342	295	259	229	210
S3M60KXD	BP480V100	6	4,866	2,801	1,955	1,495	1,206	1,008	754	599	494	418	362	318	282	259

All runtime values are shown in minutes.