



S3M80KXD Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			5kW	10kW	15kW	20kW	25kW	30kW	35kW	40kW	45kW	50kW	55kW	60kW	65kW	72kW
S3M80KXD	BP480V40	1	164	74	45	32	24	19	15	13	11	9.5	8.3	7.3	6.5	5.6
S3M80KXD	BP480V40	2	361	171	107	76	58	46	38	32	27	24	21	19	17	15
S3M80KXD	BP480V40	3	561	272	173	124	95	76	63	54	46	40	36	32	29	25
S3M80KXD	BP480V40	4	760	376	242	175	135	108	90	77	66	58	52	46	42	37
S3M80KXD	BP480V40	5	956	479	311	226	175	142	118	101	87	77	68	61	56	49
S3M80KXD	BP480V40	6	1,150	583	381	278	217	176	147	126	109	96	86	77	70	61
S3M80KXD	BP480V200	1	237	109	67	47	36	28	23	20	17	15	13	11	10	8.9
S3M80KXD	BP480V200	2	511	247	156	112	86	69	57	48	41	36	32	29	26	23
S3M80KXD	BP480V200	3	784	389	250	181	140	113	94	80	69	60	54	48	44	38
S3M80KXD	BP480V200	4	1,053	531	346	252	196	159	132	113	98	86	77	69	63	55
S3M80KXD	BP480V200	5	1,317	673	442	324	253	206	172	148	128	113	101	91	82	73
S3M80KXD	BP480V200	6	1,577	814	538	396	311	254	213	183	160	141	126	113	103	91
S3M80KXD	BP480V65	1	287	134	83	58	44	35	29	24	21	18	16	14	13	11
S3M80KXD	BP480V65	2	611	298	190	137	105	84	70	59	51	45	40	36	32	28
S3M80KXD	BP480V65	3	932	466	302	220	170	138	115	98	85	74	66	59	54	47
S3M80KXD	BP480V65	4	1,246	634	416	304	237	193	161	138	120	106	94	85	77	68
S3M80KXD	BP480V65	5	1,553	801	529	390	306	249	209	180	157	138	124	111	101	89
S3M80KXD	BP480V65	6	1,854	966	642	476	374	306	258	222	194	172	154	139	126	112
S3M80KXD	BP480V300	1	351	166	104	73	56	44	37	31	27	23	20	18	16	14
S3M80KXD	BP480V300	2	740	365	235	169	131	105	87	74	64	56	50	45	41	36
S3M80KXD	BP480V300	3	1,121	567	370	270	210	171	143	122	106	93	83	75	68	59
S3M80KXD	BP480V300	4	1,492	768	506	373	292	238	200	171	149	132	118	106	96	85
S3M80KXD	BP480V300	5	1,854	966	642	476	374	306	258	222	194	172	154	139	126	112
S3M80KXD	BP480V300	6	2,205	1,162	777	578	457	375	317	273	239	212	190	172	157	139
S3M80KXD	BP480V100	1	461	221	140	100	76	61	50	42	37	32	28	25	23	20
S3M80KXD	BP480V100	2	956	479	311	226	175	142	118	101	87	77	68	61	56	49
S3M80KXD	BP480V100	3	1,436	737	486	357	279	228	191	164	142	126	112	101	92	81
S3M80KXD	BP480V100	4	1,899	991	660	489	385	315	266	228	200	177	158	143	130	115
S3M80KXD	BP480V100	5	2,346	1,241	833	620	491	404	341	294	258	229	205	186	169	150
S3M80KXD	BP480V100	6	2,778	1,487	1,004	751	596	492	417	361	317	282	253	229	209	186

All runtime values are shown in minutes.