



## SMART3000RMOD2U Estimated Runtime

UPS	Battery Configuration	Load in Watts													
		50	100	200	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,400	2,880
SMART3000RMOD2U	Internal batteries	310	196	107	52	33	23	18	14	11	9.5	8.0	6.9	5.3	4.0

Maximum load 2880 watts without external battery packs. All runtime values are shown in minutes.

UPS	Battery Pack	BP Qty.	Load in Watts													
			50	100	200	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400
SMART3000RMOD2U	BP72V15-2U	1	863	567	326	167	108	77	60	48	40	33	28	25	22	19
SMART3000RMOD2U	BP72V18-2US	1	1,000	659	382	197	128	92	71	57	48	40	34	30	26	23
SMART3000RMOD2U	BP72V18-2US	2	1,662	1,116	661	351	232	170	133	108	90	76	65	57	50	45
SMART3000RMOD2U	BP72V18-2US	3	2,292	1,559	938	507	340	251	197	161	135	114	99	86	77	68
SMART3000RMOD2U	BP72V18-2US	4	2,892	1,987	1,209	663	448	333	263	216	181	154	134	117	104	93
SMART3000RMOD2U	BP72V28RT-3U	1	1,401	935	550	289	190	139	108	87	72	61	52	46	40	36
SMART3000RMOD2U	BP72V28RT-3U	2	2,414	1,646	992	538	361	268	210	172	144	122	106	92	82	73

Maximum load 2400 watts with external battery packs. All runtime values are shown in minutes.