



SMX1500XLRT2U Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		20	50	100	200	300	400	500	600	700	800	900	1,000	1,100	1,350
SMX1500XLRT2U	INCLUDED BATTERIES	415	221	118	57	36	26	20	16	13	11	9.1	7.8	6.8	4.9

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			20	50	100	200	300	400	500	600	700	800	900	1,000	1,100	1,200
SMX1500XLRT2U	BP36V15-2U	1	1,300	731	410	207	133	96	74	59	49	41	35	30	26	23
SMX1500XLRT2U	BP36V27-2US	1	1,724	984	559	287	187	136	105	85	70	58	50	43	38	34
SMX1500XLRT2U	BP36V27-2US	2	2,918	1,716	1,002	531	353	260	204	166	138	116	100	87	77	69
SMX1500XLRT2U	BP36V27-2US	3	4,004	2,409	1,432	774	521	387	306	250	210	178	153	134	119	106
SMX1500XLRT2U	BP36V27-2US	4	4,997	3,065	1,849	1,013	688	515	409	336	283	241	208	183	162	146
SMX1500XLRT2U	BP36V27-2US	5	5,907	3,688	2,252	1,249	853	642	512	423	357	304	264	232	207	186
SMX1500XLRT2U	BP36V27-2US	6	6,744	4,278	2,643	1,480	1,017	769	615	509	432	368	320	282	252	227
SMX1500XLRT2U	BP36V27-2US	7	7,518	4,840	3,022	1,708	1,180	895	717	596	506	433	377	333	297	268
SMX1500XLRT2U	BP36V27-2US	8	8,234	5,374	3,390	1,932	1,340	1,020	819	682	580	497	433	383	343	309
SMX1500XLRT2U	BP36V27-2US	9	8,899	5,884	3,746	2,152	1,499	1,143	920	768	654	561	490	434	388	351
SMX1500XLRT2U	BP36V27-2US	10	9,519	6,369	4,091	2,368	1,655	1,266	1,021	853	728	625	546	484	434	393
SMX1500XLRT2U	BP36V42-3U	1	3,068	1,810	1,060	564	375	277	217	177	148	124	107	93	82	74
SMX1500XLRT2U	BP36V42-3U	2	5,247	3,234	1,957	1,076	732	549	436	359	303	257	223	196	174	156
SMX1500XLRT2U	BP36V42-3U	3	7,061	4,506	2,796	1,572	1,083	820	656	544	461	394	343	302	270	243
SMX1500XLRT2U	BP36V42-3U	4	8,595	5,649	3,581	2,050	1,425	1,086	873	728	619	531	463	410	367	332
SMX1500XLRT2U	BP36V42-3U	5	9,909	6,681	4,316	2,510	1,759	1,347	1,088	909	776	667	584	518	465	421
SMX1500XLRT2U	BP36V42-3U	6	11,047	7,617	5,007	2,954	2,084	1,604	1,299	1,089	932	803	704	626	562	510
SMX1500XLRT2U	BP36V42-3U	7	12,042	8,471	5,656	3,382	2,401	1,855	1,508	1,267	1,086	938	823	733	659	598
SMX1500XLRT2U	BP36V42-3U	8	12,920	9,252	6,269	3,795	2,711	2,102	1,713	1,442	1,239	1,071	942	839	756	687
SMX1500XLRT2U	BP36V42-3U	9	13,700	9,969	6,846	4,194	3,013	2,344	1,914	1,615	1,390	1,203	1,059	945	852	775
SMX1500XLRT2U	BP36V42-3U	10	14,398	10,631	7,393	4,579	3,307	2,582	2,113	1,786	1,539	1,334	1,176	1,050	948	863

All runtime values are shown in minutes.