



SU20K3/3 Estimated Runtime

UPS	Battery Configuration	Load in Watts															
		1,000	2,000	3,000	4,000	5,000	6,000	7,000	8,000	9,000	10,000	11,000	12,000	13,000	14,000	15,000	16,000
SU20K3/3	Included Batteries	151	76	49	35	27	21	17	13	12	11	10	8.6	7.7	6.9	6.2	5.0
SU20K3/3	(1) SURBC2030	242	125	81	58	45	36	30	25	22	19	17	13	13	12	11	10
SU20K3/3	(2) SURBC2030	334	175	115	83	64	52	43	36	32	28	25	22	20	18	16	15
SU20K3/3	(1) SUBF2030 & (3) SURBC2030	427	227	150	109	85	68	57	42	41	37	33	25	24	23	20	17
SU20K3/3	(1) SUBF2030 & (4) SURBC2030	520	280	185	136	106	86	72	61	53	46	41	37	33	30	28	26
SU20K3/3	(1) SUBF2030 & (5) SURBC2030	613	332	222	163	127	103	86	74	64	56	50	45	41	37	34	31
SU20K3/3	(1) SUBF2030 & (6) SURBC2030	706	385	258	191	149	122	102	87	76	67	59	53	48	44	40	37
SU20K3/3	(2) SUBF2030 & (7) SURBC2030	798	438	295	218	171	140	117	101	88	77	69	62	56	51	47	43
SU20K3/3	(2) SUBF2030 & (8) SURBC2030	890	491	332	246	194	159	133	114	100	88	78	71	64	58	53	49
SU20K3/3	(2) SUBF2030 & (9) SURBC2030	981	544	369	275	216	177	149	128	112	99	88	80	72	66	60	55
SU20K3/3	(2) SUBF2030 & (10) SURBC2030	1071	597	406	303	239	196	165	142	124	110	98	88	80	73	67	62
SU20K3/3	(1) BP240V350	1171	632	421	310	242	197	165	137	121	107	96	86	77	70	64	58
SU20K3/3	(1) BP240V400	1323	720	482	357	280	228	191	160	141	126	112	101	91	83	76	68
SU20K3/3	(1) BP240V400C	1323	720	482	357	280	228	191	160	141	126	112	101	91	83	76	68
SU20K3/3	(1) BP240V500	1690	936	635	473	374	307	258	219	193	172	153	138	125	114	105	95
SU20K3/3	(1) BP240V500C	1690	936	635	473	374	307	258	219	193	172	153	138	125	114	105	95
SU20K3/3	(2) BP240V350	2039	1144	782	587	466	384	325	277	244	218	195	176	160	146	134	123
SU20K3/3	(2) BP240V400	2322	1315	904	681	543	449	381	326	288	257	230	209	189	173	159	146
SU20K3/3	(2) BP240V400C	2322	1315	904	681	543	449	381	326	288	257	230	209	189	173	159	146
SU20K3/3	(2) BP240V500	2995	1728	1201	913	732	608	518	447	395	354	319	289	264	242	223	205
SU20K3/3	(2) BP240V500C	2995	1728	1201	913	732	608	518	447	395	354	319	289	264	242	223	205
SU20K3/3	(3) BP240V500	4174	2476	1747	1342	1085	908	778	676	600	539	487	444	406	374	345	320
SU20K3/3	(3) BP240V500C	4174	2476	1747	1342	1085	908	778	676	600	539	487	444	406	374	345	320
SU20K3/3	(4) BP240V500	5243	3181	2271	1758	1430	1202	1034	903	804	723	656	599	549	506	469	436
SU20K3/3	(4) BP240V500C	5243	3181	2271	1758	1430	1202	1034	903	804	723	656	599	549	506	469	436

All runtime values are shown in minutes.