



## SU20K3/3XR5 Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Battery Pack Housing	BP Housing Qty	Load in Watts													
					3,000	4,000	5,000	6,000	7,000	8,000	9,000	10,000	11,000	12,000	13,000	14,000	15,000	16,000
SU20K3/3XR5	Included bateries	0	n/a	0	150	109	85	68	57	42	41	37	33	25	24	23	20	17
SU20K3/3XR5	SURBC2030	1	n/a	0	185	136	106	86	72	61	53	46	41	37	33	30	28	26
SU20K3/3XR5	SURBC2030	2	n/a	0	222	163	127	103	86	74	64	56	50	45	41	37	34	31
SU20K3/3XR5	SURBC2030	3	n/a	0	258	191	149	122	102	87	76	67	59	53	48	44	40	37
SU20K3/3XR5	SURBC2030	4	SUBF2030	1	295	218	171	140	117	101	88	77	69	62	56	51	47	43
SU20K3/3XR5	SURBC2030	5	SUBF2030	1	332	246	194	159	133	114	100	88	78	71	64	58	53	49
SU20K3/3XR5	SURBC2030	6	SUBF2030	1	369	275	216	177	149	128	112	99	88	80	72	66	60	55
SU20K3/3XR5	SURBC2030	7	SUBF2030	1	406	303	239	196	165	142	124	110	98	88	80	73	67	62
SU20K3/3XR5	SURBC2030	8	SUBF2030	2	443	331	262	215	182	156	137	121	108	98	88	81	74	68
SU20K3/3XR5	SURBC2030	9	SUBF2030	2	480	359	285	234	198	170	149	132	118	107	97	88	81	75
SU20K3/3XR5	SURBC2030	10	SUBF2030	2	517	388	308	254	214	185	162	143	128	116	105	96	88	81
SU20K3/3XR5	SURBC2030	11	SUBF2030	2	554	416	331	273	231	199	174	155	139	125	114	104	95	88
SU20K3/3XR5	SURBC2030	12	SUBF2030	3	591	445	354	292	247	214	187	166	149	135	122	112	103	95
SU20K3/3XR5	SURBC2030	13	SUBF2030	3	627	473	377	311	264	228	200	178	159	144	131	120	110	102
SU20K3/3XR5	SURBC2030	14	SUBF2030	3	664	502	400	331	281	243	213	189	170	154	140	128	118	109
SU20K3/3XR5	SURBC2030	15	SUBF2030	3	701	530	423	350	297	257	226	201	180	163	149	136	125	116

All runtime values are shown in minutes.