



## SU2200RTXLCDTAA Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,200	1,400	1,600	1,800
SU2200RTXLCDTAA	Internal batteries	n/a	141	70	45	32	25	20	16	14	12	10	7.8	6.1	4.9	4.0
SU2200RTXLCDTAA	BP48V242UTAA	1	486	258	170	124	96	78	65	55	48	42	33	27	23	19
SU2200RTXLCDTAA	BP48V60RT3UTAA	1	970	533	359	267	210	172	144	124	108	95	76	63	53	46
SU2200RTXLCDTAA	BP48V60RT3UTAA	2	1,766	1,000	688	519	414	342	290	251	220	195	157	131	112	97
SU2200RTXLCDTAA	BP48V60RT3UTAA	3	2,516	1,453	1,011	770	618	514	438	381	336	298	243	203	174	152
SU2200RTXLCDTAA	BP48V60RT3UTAA	4	3,223	1,892	1,328	1,018	821	686	587	511	452	403	330	277	238	208
SU2200RTXLCDTAA	BP48V60RT3UTAA	5	3,890	2,315	1,638	1,261	1,022	856	734	642	569	508	417	352	303	266
SU2200RTXLCDTAA	BP48V60RT3UTAA	6	4,521	2,725	1,940	1,501	1,219	1,024	881	771	685	613	504	427	369	324
SU2200RTXLCDTAA	BP48V60RT3UTAA	7	5,118	3,122	2,236	1,736	1,414	1,191	1,026	900	800	717	592	502	434	382
SU2200RTXLCDTAA	BP48V60RT3UTAA	8	5,684	3,506	2,525	1,967	1,607	1,355	1,170	1,027	915	821	679	577	500	440
SU2200RTXLCDTAA	BP48V60RT3UTAA	9	6,222	3,878	2,807	2,193	1,796	1,518	1,312	1,154	1,029	924	765	651	565	498
SU2200RTXLCDTAA	BP48V60RT3UTAA	10	6,733	4,238	3,082	2,416	1,983	1,678	1,453	1,279	1,142	1,026	852	726	631	557

All runtime values are shown in minutes.