



## SU5000RT3UHV Estimated Runtime

### Load in Watts

UPS	Battery Pack	BP Qty.	500W	1000W	1200W	1400W	1600W	1800W	2000W	2200W	2400W	2600W	2800W	3000W	3200W	3500W
SU5000RT3UHV	Included Battery Pack	0	86	39	31	26	22	19	16	14	13	12	10	9.5	8.7	8.0
SU5000RT3UHV	BP240V10RT3U	1	288	139	113	94	81	70	62	55	49	45	41	37	34	31
SU5000RT3UHV	BP240V10RT3U	2	591	296	244	206	178	155	137	123	111	101	92	85	78	70
SU5000RT3UHV	BP240V10RT3U	3	799	408	337	286	248	217	193	173	156	142	130	120	111	100
SU5000RT3UHV	BP240V10RT3U	4	1005	519	431	367	318	280	249	224	203	185	170	157	145	131
SU5000RT3UHV	BP240V10RT3U	5	1208	630	525	448	390	344	306	276	250	229	210	194	180	162
SU5000RT3UHV	BP240V557C-1PH	1	1316	681	567	483	419	370	329	296	268	245	225	208	193	174
SU5000RT3UHV	BP240V787C-1PH	1	2034	1084	908	779	681	603	540	487	444	407	375	348	324	293
SU5000RT3UHV	BP240V1037C-1PH	1	2348	1263	1061	912	799	709	635	574	524	481	444	412	384	348
SU5000RT3UHV	BP240V557C-1PH	2	2492	1346	1132	974	853	758	679	615	561	515	476	442	412	373
SU5000RT3UHV	BP240V1407C-1PH	1	3089	1696	1431	1236	1086	967	869	788	720	663	613	570	532	484
SU5000RT3UHV	BP240V787C-1PH	2	3769	2103	1782	1544	1360	1214	1093	993	910	838	777	723	676	616
SU5000RT3UHV	BP240V1037C-1PH	2	4307	2433	2067	1795	1584	1416	1277	1162	1066	983	912	850	796	725
SU5000RT3UHV	BP240V1407C-1PH	2	5533	3211	2745	2394	2122	1903	1722	1571	1444	1335	1241	1159	1086	993
SU5000RT3UHV	BP240V1407C-1PH	3	7525	4556	3931	3454	3080	2776	2522	2310	2131	1976	1842	1724	1620	1485
SU5000RT3UHV	BP240V1407C-1PH	4	9178	5757	5006	4427	3966	3590	3274	3009	2782	2587	2416	2267	2134	1961

All runtime values are in minutes.