



SU5000RT4UHVTA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			200	400	600	800	1,000	1,200	1,500	1,800	2,000	2,500	3,000	3,500	4,000	4,500
SU5000RT4UHVTA	Included batteries	0	176	91	58	42	32	25	19	15	13	9.4	7.1	5.5	4.3	3.5
SU5000RT4UHVTA	BP192V5RT2U	1	368	198	131	96	74	60	46	37	32	24	19	16	13	11
SU5000RT4UHVTA	BP192V12RT3UTAA	1	639	354	238	176	138	113	87	70	62	47	37	31	26	22
SU5000RT4UHVTA	BP192V12RT3UTAA	2	1096	622	426	320	254	209	163	133	118	90	72	59	50	43
SU5000RT4UHVTA	BP192V12RT3UTAA	3	1538	888	615	466	372	308	242	198	176	136	109	91	77	66
SU5000RT4UHVTA	BP192V12RT3UTAA	4	1967	1150	803	612	491	408	323	265	236	184	148	123	105	91
SU5000RT4UHVTA	BP192V12RT3UTAA	5	2381	1406	988	756	609	508	404	333	297	232	188	157	134	116
SU5000RT4UHVTA	BP192V12RT3UTAA	6	2782	1658	1172	900	727	608	485	401	359	281	228	191	163	142
SU5000RT4UHVTA	BP192V12RT3UTAA	7	3170	1906	1352	1042	844	707	566	469	420	330	269	226	193	168
SU5000RT4UHVTA	BP192V12RT3UTAA	8	3546	2148	1531	1183	961	806	646	537	482	379	310	260	224	195
SU5000RT4UHVTA	BP192V12RT3UTAA	9	3911	2386	1707	1323	1076	905	727	605	543	429	351	295	254	222
SU5000RT4UHVTA	BP192V12RT3UTAA	10	4264	2620	1881	1461	1191	1002	807	673	604	478	392	331	285	249
SU5000RT4UHVTA	BP192V557C-1PH	1	2210	1300	911	696	560	466	370	305	272	212	171	143	122	106
SU5000RT4UHVTA	BP192V557C-1PH	2	3970	2425	1736	1346	1095	921	740	616	553	437	358	301	259	227
SU5000RT4UHVTA	BP192V557C-1PH	3	5497	3457	2512	1967	1612	1363	1104	924	833	663	546	463	400	351
SU5000RT4UHVTA	BP192V557C-1PH	4	6833	4406	3242	2559	2109	1792	1458	1227	1108	886	734	624	542	477
SU5000RT4UHVTA	BP192V557C-1PH	5	8013	5281	3929	3123	2588	2206	1804	1522	1378	1107	920	784	682	603
SU5000RT4UHVTA	BP192V787C-1PH	1	2978	1783	1262	971	786	658	525	435	389	305	248	208	178	155
SU5000RT4UHVTA	BP192V787C-1PH	2	5261	3294	2388	1867	1529	1292	1045	874	787	626	515	436	377	331
SU5000RT4UHVTA	BP192V787C-1PH	3	7147	4635	3421	2705	2233	1899	1547	1302	1177	943	781	665	577	509
SU5000RT4UHVTA	BP192V787C-1PH	4	8731	5832	4370	3489	2899	2478	2031	1718	1556	1253	1043	892	777	687
SU5000RT4UHVTA	BP192V787C-1PH	5	10080	6907	5246	4223	3531	3031	2497	2120	1925	1557	1301	1115	974	863
SU5000RT4UHVTA	BP192V1037C-1PH	1	3760	2288	1634	1265	1028	864	693	577	517	408	334	281	241	211
SU5000RT4UHVTA	BP192V1037C-1PH	2	6509	4172	3060	2411	1985	1684	1369	1150	1038	830	686	583	506	445
SU5000RT4UHVTA	BP192V1037C-1PH	3	8675	5789	4335	3459	2874	2456	2013	1702	1542	1241	1033	883	769	680
SU5000RT4UHVTA	BP192V1037C-1PH	4	10425	7191	5481	4422	3703	3183	2625	2231	2027	1641	1373	1177	1029	912
SU5000RT4UHVTA	BP192V1037C-1PH	5	11869	8419	6516	5310	4477	3868	3209	2739	2494	2030	1703	1465	1284	1141
SU5000RT4UHVTA	BP192V1407C-1PH	1	4829	2999	2165	1688	1380	1164	939	785	706	560	461	389	336	294
SU5000RT4UHVTA	BP192V1407C-1PH	2	8113	5357	3990	3173	2630	2243	1834	1549	1402	1127	936	799	695	614
SU5000RT4UHVTA	BP192V1407C-1PH	3	10547	7292	5565	4494	3765	3237	2672	2271	2064	1672	1399	1200	1049	930
SU5000RT4UHVTA	BP192V1407C-1PH	4	12423	8909	6937	5676	4799	4155	3455	2955	2693	2196	1845	1589	1394	1240
SU5000RT4UHVTA	BP192V1407C-1PH	5	13914	10279	8144	6739	5745	5004	4190	3601	3291	2698	2277	1968	1731	1543

All runtime values are shown in minutes.