



SU6000RT3U Estimated Runtime

Load in Watts

UPS	Battery Pack	BP Qty.	500W	1000W	1200W	1400W	1600W	1800W	2000W	2200W	2400W	2600W	3000W	3400W	3800W	4200W
SU6000RT3U	Included Battery Pack	0	127	59	48	40	34	29	26	19	17	16	13	10.8	9.2	8.0
SU6000RT3U	BP240V10RT3U	1	376	186	152	128	110	96	85	76	68	61	51	44	38	33
SU6000RT3U	BP240V10RT3U	2	583	296	244	207	178	156	139	124	112	101	85	73	63	56
SU6000RT3U	BP240V10RT3U	3	789	407	337	287	248	218	194	174	157	143	121	104	90	80
SU6000RT3U	BP240V10RT3U	4	992	518	431	368	319	282	251	226	204	186	157	135	119	105
SU6000RT3U	BP240V10RT3U	5	1192	629	525	449	391	345	309	278	251	230	195	168	147	131
SU6000RT3U	BP240V557C-1PH	1	1386	722	601	513	446	393	352	315	285	260	220	190	166	149
SU6000RT3U	BP240V787C-1PH	1	2095	1124	942	809	707	627	564	508	461	422	360	312	275	247
SU6000RT3U	BP240V1037C-1PH	1	2406	1303	1095	943	826	733	660	595	542	496	424	369	326	292
SU6000RT3U	BP240V557C-1PH	2	2548	1386	1166	1005	881	783	705	636	579	531	454	395	349	314
SU6000RT3U	BP240V1407C-1PH	1	3139	1735	1466	1267	1114	992	896	810	739	679	583	509	451	405
SU6000RT3U	BP240V787C-1PH	2	3813	2142	1817	1575	1389	1240	1121	1017	929	855	736	645	573	515
SU6000RT3U	BP240V1037C-1PH	2	4346	2471	2102	1827	1613	1443	1307	1187	1086	1001	863	757	674	607
SU6000RT3U	BP240V1407C-1PH	2	5562	3248	2780	2427	2152	1932	1753	1597	1466	1353	1172	1032	921	832
SU6000RT3U	BP240V1407C-1PH	3	7539	4591	3966	3489	3112	2808	2558	2341	2155	1997	1739	1538	1378	1248
SU6000RT3U	BP240V1407C-1PH	4	9184	5791	5042	4462	4001	3625	3314	3042	2809	2609	2282	2026	1821	1653

All runtime values are in minutes.