



# SU6000RT4UTFTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			200	400	600	800	1,000	1,500	2,000	2,500	3,000	3,500	4,000	4,500	5,000	5,400
SU6000RT4UTFTAA	Included batteries	0	173	89	57	41	31	19	13	9.5	7.1	5.3	4.1	3.2	2.4	2.0
SU6000RT4UTFTAA	BP192V5RT2U	1	363	195	129	94	73	45	32	24	19	15	13	11	9.5	8.5
SU6000RT4UTFTAA	BP192V12RT3UTAA	1	631	348	234	173	136	85	61	46	37	30	25	22	19	17
SU6000RT4UTFTAA	BP192V12RT3UTAA	2	1082	613	420	315	249	160	115	89	71	59	50	43	37	34
SU6000RT4UTFTAA	BP192V12RT3UTAA	3	1520	875	606	458	366	238	173	134	108	89	76	66	57	52
SU6000RT4UTFTAA	BP192V12RT3UTAA	4	1943	1133	790	602	483	317	232	181	146	122	104	90	79	72
SU6000RT4UTFTAA	BP192V12RT3UTAA	5	2354	1387	973	744	599	397	292	228	185	155	132	115	101	92
SU6000RT4UTFTAA	BP192V12RT3UTAA	6	2751	1635	1154	886	715	476	352	277	225	189	161	140	124	113
SU6000RT4UTFTAA	BP192V12RT3UTAA	7	3135	1880	1332	1026	831	556	413	325	265	223	191	166	147	134
SU6000RT4UTFTAA	BP192V12RT3UTAA	8	3508	2119	1508	1165	945	635	473	374	306	257	221	193	170	156
SU6000RT4UTFTAA	BP192V12RT3UTAA	9	3869	2354	1682	1303	1059	715	534	422	346	292	251	219	194	177
SU6000RT4UTFTAA	BP192V12RT3UTAA	10	4219	2585	1854	1439	1172	793	594	471	387	326	281	246	218	199
SU6000RT4UTFTAA	BP192V787C-1PH	1	2944	1758	1243	956	773	516	382	301	245	206	176	153	135	123
SU6000RT4UTFTAA	BP192V787C-1PH	2	5208	3252	2355	1839	1505	1028	774	617	509	431	372	327	290	266
SU6000RT4UTFTAA	BP192V787C-1PH	3	7082	4580	3375	2666	2200	1523	1158	930	772	657	571	503	449	413
SU6000RT4UTFTAA	BP192V787C-1PH	4	8658	5766	4314	3441	2858	2000	1531	1237	1032	881	768	679	607	560
SU6000RT4UTFTAA	BP192V787C-1PH	5	10002	6833	5182	4168	3482	2460	1895	1537	1286	1102	963	853	765	706

All runtime values are shown in minutes.