



SU60KX Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Watts													
			2,500	6,000	9,500	13,000	16,500	20,000	23,500	27,000	30,500	34,000	37,500	41,000	44,500	48,000
SU60KX	BP480V26B	1	199	79	46	31	23	18	15	12	10	8.9	7.8	6.9	6.1	5.5
SU60KX	BP480V40C	1	325	133	79	54	40	32	26	22	18	16	14	13	11	10
SU60KX	BP480V200	1	462	193	116	80	60	48	39	33	28	24	22	19	17	16
SU60KX	BP480V300	1	670	288	175	123	93	74	61	51	44	38	34	30	27	25
SU60KX	BP480V400	1	895	392	242	171	130	104	86	72	62	55	48	43	39	35
SU60KX	BP480V500	1	1221	547	342	244	187	150	124	105	91	80	71	64	57	52
SU60KX	BP480V300	2	1360	614	385	276	212	170	141	120	104	91	81	73	66	60
SU60KX	BP480V400	2	1785	821	521	376	291	235	196	167	145	128	114	102	93	85
SU60KX	BP480V500	2	2389	1123	721	525	409	332	278	239	208	184	164	148	134	123
SU60KX	BP480V400	3	2618	1240	799	583	455	371	311	267	233	206	184	166	151	138
SU60KX	BP480V500	3	3456	1677	1094	804	632	518	436	376	329	292	262	237	216	198
SU60KX	BP480V500	4	4435	2209	1457	1080	853	702	594	514	452	402	362	328	300	275

All runtime values are shown in minutes.