



SU8000RT3UTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			1,000	1,500	2,000	2,500	3,000	3,500	4,000	4,500	5,000	5,500	6,000	6,500	7,000	7,200
SU8000RT3UTAA	Included Batteries	0	76	46	32	23	18	14	12	10	8.9	7.8	7.0	6.3	5.7	5.5
SU8000RT3UTAA	BP240V10RT3UTAA	1	184	118	84	65	52	43	36	31	27	24	21	19	17.4	16.8
SU8000RT3UTAA	BP240V10RT3UTAA	2	293	190	138	106	86	71	60	52	46	40	36	33	30	29
SU8000RT3UTAA	BP240V10RT3UTAA	3	404	264	193	150	121	101	86	74	65	58	52	47	43	41
SU8000RT3UTAA	BP240V10RT3UTAA	4	514	340	249	195	158	133	113	98	86	77	69	62	57	55
SU8000RT3UTAA	BP240V10RT3UTAA	5	624	415	307	240	196	164	141	122	108	96	86	78	71	69
SU8000RT3UTAA	BP240V10RT3UTAA	6	734	491	364	286	234	197	169	147	129	115	104	94	86	83
SU8000RT3UTAA	BP240V10RT3UTAA	7	843	566	421	332	273	230	197	172	152	136	122	111	101	98
SU8000RT3UTAA	BP240V10RT3UTAA	8	951	642	479	379	311	263	226	197	174	156	141	128	117	113
SU8000RT3UTAA	BP240V10RT3UTAA	9	1059	717	536	425	350	296	255	223	197	176	159	145	133	128
SU8000RT3UTAA	BP240V10RT3UTAA	10	1166	792	594	471	389	329	284	248	220	197	178	162	149	144
SU8000RT3UTAA	BP240V787C-1PH	1	915	617	460	363	298	252	216	189	167	149	134	122	112	108
SU8000RT3UTAA	BP240V787C-1PH	2	1823	1257	953	764	634	541	469	412	367	330	300	274	252	244
SU8000RT3UTAA	BP240V787C-1PH	3	2672	1870	1432	1156	966	828	721	637	570	515	469	430	396	384
SU8000RT3UTAA	BP240V787C-1PH	4	3465	2454	1894	1537	1291	1111	971	860	771	698	637	586	541	525
SU8000RT3UTAA	BP240V787C-1PH	5	4209	3013	2340	1908	1609	1388	1216	1080	971	880	805	741	685	665

All runtime values are shown in minutes.