


## SmartRack 2U Cantilever Fixed Shelf (60 lbs / 27.2 kgs capacity; 18-in. / 457 mm Deep)

MODEL NUMBER: **SRSHELF2P**

### Highlights

- Fixed Shelf, 2U Cantilever mount. Required mounting hardware included
- 2 or 4 post rack compatible
- 18 inch shelf depth
- Cantilever shelf supports monitors and other equipment
- Cold rolled steel with black finish.
- Use two shelves back to back to create a deep fixed shelf in 2POST racks

### Package Includes

- Shelf and mounting hardware

### Description

SmartRack® SRSHELF2P is a 2U cantilever mount fixed shelf. Cantilever shelf supports monitors and other equipment with a 60 pounds (27.2 kilograms) capacity. Shelf is compatible with 2- or 4-post rack enclosure cabinets. The SRSHELF2P is 18 inches in depth, but can use two shelves back to back to create a deep fixed shelf in 2-post racks. Required mounting hardware is included.

### Features

- 2U cantilever mount fixed shelf
- Cantilever shelf supports monitors and other equipment with a 60 lbs (27.2 kgs) capacity
- Shelf is compatible with 2 or 4 post rack enclosure cabinets
- SRSHELF2P is 18 inches in depth but can use two shelves back to back to create a deep fixed shelf in 2POST racks
- Required mounting hardware is included

## Specifications

OVERVIEW	
UPC Code	037332144614
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.10 x 19.80 x 18.70
Shipping Dimensions (hwd / cm)	10.41 x 50.29 x 47.50
Shipping Weight (lbs.)	8.06
Shipping Weight (kg)	3.66



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Dimensions (hwd / in.)	3.500 x 19.000 x 18.000
Unit Dimensions (hwd / cm)	8.89 x 48.26 x 45.72
Unit Weight (lbs.)	5
Unit Weight (kg)	2.27
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.