



Powering and Connecting Your World

EDGE INFRASTRUCTURE

Tripp Lite Makes Edge Deployment Easy with

EdgeReady™ Micro Data Centers

Tripp Lite makes it quick and easy to deploy edge infrastructure. Preconfigured EdgeReady micro data centers (MDCs) integrate a rack enclosure, UPS, PDU and remote management, with easy-to-add options for cooling, extended runtime, KVM, security and cabling. Dozens of stock configurations are available for immediate order, and options for customization are unlimited. Stock configurations ship in three days; customized models ship in as little as five. They are assembled and tested in a controlled environment, then shipped on reinforced shock pallets for safe and stable transit.

TRIPP LITE'S **EDGE**


SPEED: Only Tripp Lite ships assembled and tested MDCs three business days after order receipt.



FLEXIBILITY: Tripp Lite offers more ready-to-order MDCs than anyone, including wall-mount, compact, quiet and full-size form factors shipped as assembled/tested units or validated kits for onsite assembly; customization options are unlimited.

EXPERIENCE: Tripp Lite's team has built thousands of edge solutions, tested and proven in the field.

The edge made easy.™



KEY CUSTOMERS

- **IT and facilities managers** installing a few racks outside a data center
- **Expanding businesses** opening new offices or outlets
- **Warehouses and factories** increasing automation
- **Educational institutions** expanding IT in limited space
- **Financial institutions** equipping branch locations
- **Merging organizations** standardizing IT operations
- **Government agencies** implementing smart cities
- **Temporary sites** requiring portable/emergency IT capability
- **Content providers** equipping cellular base stations (5G)
- **Service providers** seeking IT building blocks
- **Retail and office locations** incorporating IoT

STOCK CONFIGURATIONS



Form Factor	Usable Rack Space	Output Power Capacity	UPS Type	Assembled or Kit?
Wall-Mount	9U to 15U	1.5 kVA to 3 kVA	Line-Interactive	Kit Only
Compact Floor-Standing	15U to 21U	1.5 kVA to 3 kVA	Line-Interactive	Either
Quiet Floor-Standing	15U to 21U	1.5 kVA to 3 kVA	Line-Interactive	Either
Full-Size Floor-Standing	30U to 40U	3 kVA to 10 kVA (N+N)	On-Line	Either

CUSTOMIZATION

Any stock configuration can be customized with options like active cooling, battery packs for extended runtime, PDU upgrades, KVM switches, power cords and network cabling. Tripp Lite can even customize individual components, like color-coding PDUs and power cords, adding automatic transfer switching and providing special rack cabinets for harsh environments. Custom MDCs ship as little as five days after order receipt. (Time varies with level of customization.)

WARRANTY

All models, including kits and custom configurations, include a two-year limited warranty extendable to three years.

Custom Configuration Example

Included Hardware:

- 1 Rack Enclosure With Passive Cooling
- 2 UPS System With Network Management Card
- 3 Environmental Sensor
- 4 Metered PDU

Optional Hardware:

- 5 Switched PDU (Replaces Metered PDU)
- 6 External Battery Pack
- 7 Rack-Mount Air Conditioning Unit (Active Cooling)
- 8 Console KVM

Other Options Not Shown:

Console Servers | Door Sensors
Cable Managers | Power Cords
Network Cables | Patch Panels



The edge made easy.™

Access Tripp Lite's full line of EdgeReady micro data centers and complete specifications at tripplite.com/mdc



1111 W. 35th Street, Chicago, IL 60609
solutions@tripplite.com • 773.869.1236