



Eaton's Tripp Lite series SmartPro UPS, 2U rack/tower, 750–3000 VA

Enhanced performance for reliable power protection and battery backup

The Tripp Lite series SmartPro 2U rack/tower UPS has undergone a significant enhancement in looks and features. Unity power factor, long battery runtimes, network capability and a user-friendly LCD control panel make this line-interactive UPS an outstanding value for protecting distributed IT equipment in network closets, server rooms and edge computing sites.

Power and protect IT equipment

Enhanced power for larger equipment loads

A unity power factor (1.0) enables the UPS to deliver the most watts possible at each power rating, allowing support of more equipment like servers, switches, VoIP phone systems and professional audio/video computer systems.

Effective power protection

The UPS provides pure sine wave AC output to connected equipment.

- Automatic voltage regulation (AVR) corrects abnormal voltages without switching to battery, keeping the UPS fully charged.
- Automatic restart when AC input power is restored after an outage reduces the need for onsite visits.

Reliable battery backup to prevent downtime

In the event of a power outage, switchover from line to battery power happens within milliseconds.

- User-replaceable, hot-swappable VRLA internal batteries outlast brief outages and permit graceful system shutdown during longer blackouts.
- Models with extendable runtime support up to four external battery packs (sold separately).

Easily monitor and manage UPS operation

User-friendly local monitoring and control

Status LEDs and a menu-driven LCD make it easier to identify alarms and faults. The control panel rotates to accommodate horizontal or vertical UPS installation.

Advanced remote monitoring

An optional network card (WEBCARDLXE) provides SNMP-based UPS management. Free downloadable PowerAlert software supports remote monitoring and control.

- USB and RS-232 serial ports provide additional communication options. (Cables are included.)
- RPO/ROO port allows remote shutdown or restart of connected equipment.
- Programmable outlet banks can be controlled independently.

Product support

Eaton provides free product support via phone, email or chat. If you have a question or need to find a replacement battery, Eaton can help.



Mount the UPS in a rack or use the included tower stands for vertical placement.



Powering Business Worldwide

Feature focus (See tripplite.eaton.com for model-specific configurations.)

Front panel overview (all models)




Model SMART2200RML2U shown

Back panel overview (120V models)



Model SMART2200RML2U shown

Back panel overview (208V/230V models)



Model SMX1500XLR2U shown

Specifications*

Catalog number	Rating (VA/watts)	Internal runtime (min), Full/half load	Plus 1 external battery pack** (min), Full/half load	Total Rack Size	Outlets	Input connection	Dimensions (H x W x D), in	Net weight, lb
120V, 50/60 Hz rack/tower UPS with network card slot								
SMART750RML2U	750/750	9/23	51/115	2U	(8) 5-15R	5-15P, 6 ft.	3.4 x 17.2 x 17.6	44.5
SMART1000RML2U	1000/1000	6/17	35/82	2U	(8) 5-15R	5-15P, 10 ft.	3.4 x 17.2 x 17.6	44.5
SMART1500RML2U	1440/1440	5.1/15	25/60	2U	(8) 5-15R	5-15P, 10 ft.	3.4 x 17.2 x 17.6	50.7
SMART2200RM2U	1950/1950	4/12	N/A	2U	(1) L5-20R, (6) 5-20R	5-20P, 10 ft.	3.4 x 17.2 x 23.7	65.3
SMART2200RML2U	1950/1950	4/12	26/61	2U	(1) L5-20R, (6) 5-20R	5-20P, 10 ft.	3.4 x 17.2 x 23.7	65.3
SMART3000RM2U	3000/3000	3/9	N/A	2U	(1) L5-30R, (6) 5-20R	L5-30P, 10 ft.	3.4 x 17.2 x 23.7	74.5
SMART3000RML2U	3000/3000	3/9	17/41	2U	(1) L5-30R, (6) 5-20R	L5-30P, 10 ft.	3.4 x 17.2 x 23.7	74.5
120V, 50/60 Hz rack/tower UPS network card bundles with WEBCARDLXE								
SMART750RML2UN	750/750	9/23	51/115	2U	(8) 5-15R	5-15P, 6 ft.	3.4 x 17.2 x 17.6	44.5
SMART1000RML2UN	1000/1000	6/17	35/82	2U	(8) 5-15R	5-15P, 10 ft.	3.4 x 17.2 x 17.6	44.5
SMART1500RMLN	1440/1440	5.1/15	25/60	2U	(8) 5-15R	5-15P, 10 ft.	3.4 x 17.2 x 17.6	50.7
SMART2200RM2UN	1950/1950	4/12	N/A	2U	(1) L5-20R, (6) 5-20R	5-20P, 10 ft.	3.4 x 17.2 x 23.7	65.3
SMART2200RMLN	1950/1950	4/12	26/61	2U	(1) L5-20R, (6) 5-20R	5-20P, 10 ft.	3.4 x 17.2 x 23.7	65.3
SMART3000RM2UN	3000/3000	3/9	N/A	2U	(1) L5-30R, (6) 5-20R	L5-30P, 10 ft.	3.4 x 17.2 x 23.7	74.5
SMART3000RMLN	3000/3000	3/9	17/41	2U	(1) L5-30R, (6) 5-20R	L5-30P, 10 ft.	3.4 x 17.2 x 23.7	74.5
208V/230V, 50/60 Hz rack/tower UPS with network card slot								
SMX1500XLR2UA	1500/1500	5.1/15	25/60	2U	(8) C13	C14 input	3.4 x 17.2 x 17.6	49.4
SMX3000XLR2UA	3000/3000	3/9	17/41	2U	(2) C19, (8) C13	C20 input w/ C19 to L6-20P cable	3.4 x 17.2 x 23.7	69.9
208V/230V, 50/60 Hz rack/tower UPS network card bundles with WEBCARDLXE								
SMX1500XLR2UN	1500/1500	5.1/15	25/60	2U	(8) C13	C14 input	3.4 x 17.2 x 17.6	49.4
SMX3000XLR2UN	3000/3000	3/9	17/41	2U	(2) C19, (8) C13	C20 input w/ C19 to L6-20P cable	3.4 x 17.2 x 23.7	69.9

SmartPro 2U rack/tower UPS has a two-year limited warranty (three years with registration) and \$250,000 Ultimate Lifetime Insurance. * Due to continuous improvement programs, all specifications are subject to change without notice.

** Models with extendable runtime support up to four external battery packs.

External battery packs

Catalog number	Voltage	Compatible SmartPro UPS models
BP48VRM2U	48V DC	SMART750RML2U, SMART750RML2UN, SMART1000RML2U, SMART1000RML2UN, SMART1500RML2U, SMART1500RMLN, SMX1500XLR2U, SMX1500XLR2UN
BP72VRM2U	72V DC	SMART2200RML2U, SMART2200RMLN, SMART3000RML2U, SMART3000RMLN, SMX3000XLR2UA, SMX3000XLR2UN

External battery packs have a two-year limited warranty.

Accessories

Catalog number	Description
WEBCARDLXE	Network management card

Accessories

Catalog number	Description
103007018-5591	2-post rack-mount installation kit
RK4PRS	Ship-in-rack 4-post adjustable mounting rail kit

Accessories

Catalog number	Description
E2MTI†	Temperature sensor module
E2MTDO†	Temperature sensor module with digital outputs
E2MTHDI†	Temperature and humidity sensor module with digital inputs

† Requires WEBCARDLXE.

Eaton

1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2023 Eaton
All Rights Reserved
Printed in USA
BR153164EN / 23-02-165
April 2023

EATON
Powering Business Worldwide

Learn more at
tripplite.eaton.com/SmartProUPS

Eaton, Tripp Lite, SmartPro and PowerAlert are registered trademarks.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

