



Powering and Connecting Your World

NEW PRODUCT ANNOUNCEMENT

4K Interactive Touchscreens

Encourage Collaboration and Communication with an Interactive Presentation Platform



Tripp Lite's 4K interactive touchscreens feature built-in wireless networking and an HD webcam to connect local and remote teams.

Perfect for:

Classrooms, conference rooms and huddle spaces.

Tripp Lite's interactive touchscreens provide an all-in-one presentation platform that encourages group collaboration and communication in everything from business meetings to distance learning.

The displays integrate a 4K touchscreen, wireless networking and a high-definition webcam to connect local and remote teams in corporate, education, healthcare, commercial, hospitality, retail and government settings. Users can share ideas from any location, allowing organizations with work-from-home and learn-from-home strategies to thrive.

Available in 55-inch and 65-inch sizes, the touchscreens provide a level of engagement that basic electronic whiteboards cannot match.

Key Benefits

VERSATILE COMPATIBILITY

- Embedded Android operating system is compatible with a wide array of applications and hardware, including Windows, Android, Chrome, iOS and MacOS devices.
- 65-inch touchscreen includes a full-featured, touch-enabled Windows 10 PC for even more functionality.
- VESA-compliant mounting hole patterns make installation easy on a compatible wall mount or rolling TV/monitor cart.

DYNAMIC INTERACTIVITY

- Patented touchscreen technology provides a low-latency, ultra-fast response to fingers or the included stylus pens.
- Touchscreens have 20 points of multi-touch to accommodate multiple concurrent users.

COLLABORATIVE COMMUNICATION

- Wireless networking allows anyone to participate in meetings, presentations and group discussions from any location.
- Detachable 1080p HD webcam with wide-angle view and noise-cancelling microphone captures the entire meeting area.
- Remote screen sharing capability increases opportunities for audience engagement.

AUDIOVISUAL EXCELLENCE

- Large, bright, razor-sharp 4K display and two 20-watt soundbar speakers with subwoofer provide a best-in-class presentation platform.

Feature Focus



A Wi-Fi Connectivity

Antennas enable connection to a wireless network.



B HD Webcam

Detachable webcam with microphone supports 1080p video resolutions. A wide-angle view captures the entire meeting area.



C 4K Touchscreen

Screen accepts up to 20 simultaneous touch inputs to support multiple users.



D Front-Panel Controls

Buttons offer source and menu selection, volume adjustment and touch enablement.



E Input and Output Ports

Ports on the front and rear panels provide connections for peripherals and HDMI, DisplayPort and VGA video sources. See Specifications below.



Remote Control

Use the remote control to access the touchscreen display. Front-panel buttons and on-screen display menus offer other control options.



Stylus Pens

Two pens and replacement tips are included.



SPECIFICATIONS



Model	DMTP55NO	DMTP65OPS
Screen Size	55 in.	65 in.
Maximum Video Resolution	3840 x 2160 @ 60 Hz	3840 x 2160 @ 60 Hz
Number of Touch Points	20	20
Operating System	Android	Android
Built-In PC	—	Windows 10; 8 GB of RAM (upgradable to 32 GB)
Input Ports	Front: HDMI; USB 2.0; USB for touch Rear: (3) HDMI; DisplayPort; VGA; USB for camera; (3) USB 2.0 – Android only; (2) USB for touch; (2) 3.5 mm audio	Front: HDMI; USB 2.0; USB for touch Rear: (3) HDMI; DisplayPort; VGA; USB for camera; (3) USB 2.0 – Android only; (2) USB 2.0; (2) USB 3.0; (2) USB for touch; (3) 3.5 mm audio
Output Ports	Rear: HDMI; 3.5 mm audio	Rear: (2) HDMI; (2) 3.5 mm audio
Ethernet Interface	RJ45	(2) RJ45
Serial Interface	RS-232 (DB9)	RS-232 (DB9)
Wireless Interface	4 large antennas	4 large antennas, 2 small antennas
Control Options	Remote control, front-panel buttons, on-screen menus/touch input	Remote control, front-panel buttons, on-screen menus/touch input
Input Voltage	120V	120V
Power Cord Lg.	6 ft. (1.8 m)	6 ft. (1.8 m)
Overall H x W x D	32.3 x 50.4 x 3.6 in. (820.1 x 1280.4 x 91.4 mm)	36.7 x 58.7 x 3.62 in. (932 x 1491 x 92 mm)
Limited Warranty	2 Years	2 Years

Learn more about Tripp Lite's full line of interactive touchscreens at triplite.com.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | triplite.com