



NEW PRODUCT ANNOUNCEMENT

AC Charging Carts

Charge, Secure and Organize up to 21 or 27 Chromebooks in a Slim Cart



Model: CSC21AC

Perfect for:

Classrooms, corporate offices,
medical facilities, retail stores and warehouses.

Tripp Lite's new CSC21AC and CSC27AC charging carts provide mid-size options for charging Chromebooks, laptops, tablets, smartphones and other portable electronics. Accommodating up to 21 or 27 devices, the carts offer high-speed charging, secure organization and multipurpose functionality. Both carts have a narrower cabinet than larger capacity models to save space and make handling and placement easier, especially in tight areas.

Key Benefits

HIGH-SPEED CHARGING

- Each device's power adapter has a dedicated AC outlet.

COMPREHENSIVE PROTECTION

- Steel cabinet has key-locking front and rear compartments to store devices and power adapters separately.
- Front door can be fastened with a user-supplied padlock for extra security.
- Flow-through ventilation helps prevent overheating.
- Corner safety bumpers protect walls and doorways from damage.
- Protective shelf finish helps prevent device scratches.

CLUTTER-REDUCING ORGANIZATION

- Device slots are numbered and have removable dividers.
- Built-in cable managers and removable storage baskets keep cables and power adapters in order.

CONVENIENT MOBILITY

- Swivel casters have large, non-marking wheels for smooth handling over uneven surfaces. The casters lock to help prevent movement at rest.
- Slim design saves space and fits through narrow doorways.
- Wide-grip handle assists cart control.
- Input cord wrap keeps the power cord out of the way during movement.

ENHANCED WORKSTATION FEATURES


- Solid laminate wood-grain worktop acts as a writing surface or a platform for A/V equipment.
- Cat6 RJ45 pass-through allows connection to an external Ethernet network to set up a user-supplied wireless access point inside the cart.

Feature Focus Model: CSC21AC


FRONT



Solid Laminate Wood-Grain Worktop & Wide-Grip Handle



3-Point Lock (Front & Rear Doors)



FRONT



Cable Manager

Padlock Hasp



Numbered Device Slots

REAR



Removable Storage Baskets for Power Adapters




Power Strip with NEMA 5-15R Outlets and a Circuit Breaker



Corner Safety Bumpers & Locking Swivel Casters with Non-Marking Wheels

SIDE



Cat6 RJ45 Pass-Through

Input Cord Wrap

SPECIFICATIONS

Model	CSC21AC	CSC27AC
Form Factor	AC Cart	AC Cart
Compatible Devices	Chromebooks, Laptops, Tablets and Smartphones	Chromebooks, Laptops, Tablets and Smartphones
No. of Device Slots	21	27
Maximum Screen Size ⁽¹⁾	≤15 in. (≤38 cm)	≤15 in. (≤38 cm)
Device Slot Size (HxWxD)	10.13 x 1.63 x 15.58 in. (257 x 41.4 x 395.67 mm)	10.13 x 1.2 x 15.58 in. (257 x 30.48 x 395.67 mm)
Charging Method	27 AC Outlets (NEMA 5-15R)	27 AC Outlets (NEMA 5-15R)
Charging Capacity	1440 W	1440 W
Primary Construction	Powder-Coated Steel	Powder-Coated Steel
Security	3-Point Locks (Front & Rear), Optional Padlock (Front)	3-Point Locks (Front & Rear), Optional Padlock (Front)
Wireless Syncing	Compatible	Compatible
AC Input	120V, 60 Hz	120V, 60 Hz
Input Cord Length/Plug Type	10 ft./Right-Angle NEMA 5-15P Plug	10 ft./Right-Angle NEMA 5-15P Plug
Workstation Features	Solid Laminate Worktop, RJ45 Pass-Through	Solid Laminate Worktop, RJ45 Pass-Through
Unit Dimensions with Handle (HxWxD)	43.28 x 15.85 x 28.71 in. (1099.31 x 402.62 x 729.3 mm)	43.28 x 15.85 x 28.71 in. (1099.31 x 402.62 x 729.3 mm)
Limited Warranty (Extended Warranty Available)	2 Years	2 Years

(1) Depends on device dimensions.



Learn more about Tripp Lite's full line of Charging Stations & Carts at www.triplite.com/cs.



Tripp Lite Corporate Headquarters
1111 W. 35th Street, Chicago, IL 60609 USA
773.869.1773 | www.triplite.com