



# Pop-Out Security Video Wall Mounts

Powering and Connecting Your World

## Install and Adjust Video Walls More Easily



*Tripp Lite's new display mounts are a hassle-free way to create sleek, engaging video walls.*

### Perfect for:

Professional-quality video walls of any shape or size in airports, arenas, convention centers, bars and restaurants.

Tripp Lite's new display mounts make professional-quality video walls more convenient to create and manage. By giving installers the ability to fine-tune the positioning of 45- to 70-inch screens, they make it easier to achieve a seamless video wall presentation. The mounts feature a pop-out design that allows them to extend away from the wall, creating space to access cables, make adjustments and replace screens.

A landscape screen orientation display mount and a portrait screen orientation display mount are available. Both include brackets with VESA-compliant screen-mounting patterns. Their included combination locks deter against tampering and theft for a secure video wall that is easy to customize.

## Key Benefits

### PURPOSE-BUILT SOLUTION FOR VIDEO WALLS

- Pop-out design allows convenient rear access in video wall applications where displays are mounted edge-to-edge.
- Mounts accommodate displays from 45" to 70" and up to 154 lb.
- Models are available for landscape and portrait orientations.

### POST-INSTALLATION MICRO-ADJUSTABILITY

- In addition to tilt and lateral adjustments, the mounts feature up-and-down and in-and-out micro-adjustments for perfect alignment.
- Kickstands help with tilt access for easy cable management and display replacement.


### DURABLE CONSTRUCTION

- Heavy-duty steel frame withstands the stress of frequent adjustments.
- Black powder-coated finish offers durability and scratch resistance.
- Four-position combination lock helps protect displays against theft in public spaces.


### VESA COMPLIANCE

- VESA-compliant mounting brackets are compatible with displays from most manufacturers for hassle-free mounting.

# Feature Focus



Model: DWMSCL4570VW



Model: DWMSCP4570VW

## A VESA-Compliant Brackets

Brackets are compatible with 200x200, 200x400, 400x200, 300x300, 400x400, 400x600 and 600x400 VESA mounting patterns.

## B Pop-Out Module

Pop-out design is ideal for accessing cables in tight video wall installations.

## C VESA Adapters

Optional adapters can be added to accommodate the larger screen sizes (DWMSCP4570VW only).

## D Kickstands

Kickstands make tilt access to the display more convenient.

## E Combination Lock

Four-position combination lock secures the display bracket to the mount.



## F Micro Adjustment

Screws and knobs allow installers to fine-tune screen alignment with ease.

## G Handles

Handles provide tilt adjustment for optimal viewing angles.

## H Anti-Skid Blocks

Blocks secure display position after adjustments.



## SPECIFICATIONS



Model	DWMSCL4570VW	DWMSCP4570VW
Orientation	Landscape	Portrait
Motion	Full	Full
Supported Screen Sizes	45 to 70 in. (114 to 178 cm)	45 to 70 in. (114 to 178 cm)
Weight Capacity	154 lb. (70 kg)	154 lb. (70 kg)
Mounting Profile (Surface to Display)	5.6 to 12.1 in. (14 to 31 cm)	6.0 to 12.4 in. (15 to 31 cm)
Supported VESA Patterns (mm)	200x200, 300x300, 400x200, 400x400, 600x400	200x200, 200x400, 300x300, 400x400*, 400x600*
Tilt Adjustment	+3° to -5°	+3° to -5°
Construction	Powder-Coated Steel	Powder-Coated Steel
Combination Lock (Included)	Four Position	Four Position
Kickstands	Yes	Yes
Warranty	5-Year Limited	5-Year Limited

\*Requires the included adapter brackets.

Learn more about Tripp Lite's full line of display mounts at [triplite.com](http://triplite.com).



Tripp Lite Corporate Headquarters  
1111 West 35th Street, Chicago, IL 60609 USA  
773.869.1773 | [triplite.com](http://triplite.com)