

Chromebook & Tablet CHARGING STATIONS & CARTS

PERFECT FOR: iPad® | Android™ | Kindle™ | Surface™ | Chromebook™ | MacBook® | Ultrabook™

Charge, Sync, Secure and Organize up to 36 Chromebooks or 48 Tablets



FAST CHARGING/SYNCING

- USB: Up to 2.4 amps per device, plus syncing
- AC: Dedicated outlet for each device

COMPREHENSIVE PROTECTION


- Locking steel enclosure
- Flow-through ventilation
- Non-scratching shelves

EASY ORGANIZATION

- Removable device dividers
- Built-in cord management
- Slots hold laptops up to 17 inches

FLEXIBLE DEPLOYMENT

- Mobile cart or station with cart option
- Optional wall/desk/table mounting
- Black or white powder-coated finish



SEE NEXT PAGE FOR FEATURES AND SPECS



Tripp Lite Chromebook & Tablet Charging Stations & Carts

2-Year Limited WARRANTY

Extended warranties available.



Recommended Use	Charging and Syncing Tablets (iPad, Android, Kindle)				Charging Chromebooks and Laptops		
Black Model	CSC32USB	CSC16USB	CS48USB	CS16USB	CSC36AC	CSC32AC	CSC16AC
White Model	CSC32USBW	—	CS48USBW	CS16USBW	—	CSC32ACW	CSC16ACW
Form Factor	USB Cart	USB Cabinet	USB Cabinet	USB Cabinet	AC Cart	AC Cart	AC Cabinet
Device Capacity	32 Tablets	16 Tablets	48 Tablets	16 Tablets	36 Laptops	32 Laptops	16 Laptops
Charging Method	32 USB Ports	16 USB Ports	48 USB Ports	16 USB Ports	36 AC Outlets with Dual-Zone Charging ⁽⁴⁾	32 AC Outlets	16 AC Outlets
Charging Capacity ⁽¹⁾	2.4A per Port	2.4A per Port	2.4A per Port	2.4A per Port	1,440W per Zone ⁽⁴⁾	1,440W Total	1,440W Total
Maximum Screen Size ⁽²⁾	≤17 in. Laptop	≤17 in. Laptop	≤12 in. Tablet	≤12 in. Tablet	≤15 in. Laptop	≤17 in. Laptop	≤17 in. Laptop
Device Slot Size ⁽³⁾ (HWD)	10.5x1.5x15.4 in.	10.5x1.5x15.4 in.	8.0x0.8x13.9 in.	8.1x0.8x13.9 in.	10.5x1.5x15.4 in.	10.5x1.5x15.4 in.	10.6x1.5x15.4 in.
Cart Configuration with Non-Marking Wheels	Included	Add CSHANDLEKIT2	Add CSHANDLEKIT	—	Included	Included	Add CSHANDLEKIT2
Wall-Mount Option	✓	✓	✓	✓	—	✓	✓
Primary Construction	Powder-Coated Steel	Powder-Coated Steel	Powder-Coated Steel	Powder-Coated Steel	Powder-Coated Steel	Powder-Coated Steel	Powder-Coated Steel
Security	3-Point Lock, Padlock/Cable Lock ⁽⁵⁾	3-Point Lock, Padlock/Cable Lock ⁽⁵⁾	3-Point Lock and Locking Side Panels	Locking Door and Side Panels	3-Point Locks for Front and Back	3-Point Lock, Padlock/Cable Lock ⁽⁵⁾	3-Point Lock, Padlock/Cable Lock ⁽⁵⁾
Tablet Compatible	✓	✓	✓	✓	✓	✓	✓
Wired USB Syncing	✓	✓	✓	✓	—	—	—
Wireless Syncing	Compatible	Compatible	Compatible	Compatible	Compatible	Compatible	Compatible
AC Input	110-240V, 50/60 Hz	110-120V, 50/60 Hz	110-240V, 50/60 Hz	110-240V, 50/60 Hz	120V, 60 Hz	120V, 50/60 Hz	120V, 50/60 Hz
Input Cord Length	10 ft.	10 ft.	10 ft.	10 ft.	10 ft.	10 ft.	10 ft.
Front Door Type	Split/Double	Split/Double	Single	Single	Single	Split/Double	Split/Double
Flow-Through Ventilation	✓	✓	✓	✓	✓	✓	✓
Built-in Cord Management	✓	✓	✓	✓	✓	✓	✓
Toolless Access Panel(s)	✓	✓	—	—	✓	✓	✓
Non-Scratch Shelf Finish	✓	✓	✓	✓	✓	✓	✓
Removable Dividers	✓	✓	✓	✓	✓	✓	✓
Workstation Features	Solid Worktop	Solid Worktop	—	—	Solid Laminate Worktop, RJ45 Pass-Through, 3 Auxiliary Outlets (2 External)	Solid Worktop	Solid Worktop
Unit Dimensions (HWD)	36.1x34.8x21.6 in.	18.8x30.3x21.6 in.	35.6x23.6x21.6 in.	14.6x23.6x17.7 in.	42.3 x 28 x 26.1 in.	42.3x34.8x21.6 in.	18.8x30.3x21.6 in.

Certifications vary with model. (1) 1.5A during wired syncing. (2) Depends on device dimensions. (3) CSC models have extra 1.1 in. depth inside door. CS models have extra 1.5 in. (4) Active charging alternates between zones hourly. (5) User-supplied.

Also Available



CS32AC

AC Charging Station for 32 Tablets



CSC32USB

USB Charging Station for 32 Tablets



NEW! CSD1006AC

AC Desktop Charging Station for 10 Laptops or Tablets



NEW! CSD1006USB

USB Desktop Charging Station for 10 Tablets

Learn more at
www.tripplite.com/cs



Tripp Lite World Headquarters
1111 W. 35th Street, Chicago, IL 60609 USA
773.869.1236 • solutions@tripplite.com

