

Keep Your Home Theatre Streaming

Tripp Lite Power Protection Can Help



Safe, reliable and convenient power solutions from Tripp Lite help ensure your home entertainment keeps up with demand.



UPS SYSTEMS

Make sure all your home theatre equipment is protected and receiving clean power.

Model	Load Capacity	Outlets (Type)	LCD	Cord Length (Plug Type)	Single-PC Runtime(3)	1/2 Load Runtime(4)	Comm. Port	Unit Dimensions (mm)
OMNIVSX1500	1500 VA (900W)	8 (C13)	Yes	Inlet (C14)(1)	112 min.	6,5 min.	USB(5)	183 x 130 x 320
OMNIVSX1500D	1500 VA (900W)	4 (Schuko)	Yes	1.5 m (Schuko)(2)	112 min.	6,5 min.	USB(5)	183 x 130 x 320
OMNIVSX1000	1000 VA (600W)	8 (C13)	Yes	Inlet (C14)(1)	50 min.	5 min.	USB(5)	160 x 122 x 345
OMNIVSX1000D	1000 VA (600W)	4 (Schuko)	Yes	1.5 m (Schuko)(2)	50 min.	5 min.	USB(5)	160 x 122 x 345
OMNIVSX850	850 VA (480W)	6 (C13)	Yes	Inlet (C14)(1)	46 min.	5 min.	USB(5)	160 x 122 x 345
OMNIVSX850D	850 VA (480W)	4 (Schuko)	Yes	1.5 m (Schuko)(2)	46 min.	5 min.	USB(5)	160 x 122 x 345
OMNIVSX650	650 VA (360W)	4 (C13)	LEDs	Inlet (C14)(1)	42 min.	6 min.	None	142 x 102 x 300
OMNIVSX650D	650 VA (360W)	2 (Schuko)	LEDs	1.5 m (Schuko)(2)	42 min.	6 min.	None	142 x 102 x 300
OMNIVSX450	450 VA (240W)	4 (C13)	LEDs	Inlet (C14)(1)	32 min.	7 min.	None	142 x 102 x 300
OMNIVSX450D	450 VA (240W)	2 (Schuko)	LEDs	1.5 m (Schuko)(2)	32 min.	7 min.	None	142 x 102 x 300

All models: 230V AC, 50/60 Hz nominal input and output. Replaceable internal battery. 2-year limited warranty. (1) The C14 inlet connects to a user-supplied cord and plug compatible with local AC outlets. The UPS includes 2 x 1,5 m C13-to-C14 power cords. This allows the user to disconnect a grounded power cord from a device, use that cord to connect the UPS to the wall outlet and use an included C13-to-C14 power cord to connect the device to the UPS. (2) CEE 7/7. (3) Estimated battery backup runtime for energy-efficient PC requiring 60W continuous. (4) Estimated. (5) USB cable included.

SURGE & POWER STRIPS

Keep your power cords organised and out of sight. Select power strips feature surge protection for peace of mind against power surges, spikes and line noise.



Model	AC Voltage	Amperage	AC Input Frequency	Outlet Style (Quantity)	Cord Length	Housing Dimensions (mm)	Unit Weight	Surge Protection	USB-A Charge	Warranty
Surge Protector										
TLP6B18	220-250V	13A	50/60 Hz	BS1363A (6)	1.8 m	429 x 60 x 33	0.5 kg	250 Joules	-	Lifetime Limited
Power Strips										
PS1B	220-250V	13A	50/60 Hz	BS1363A (2)	N/A	51 x 50 x 71	0.1 kg	-	-	Lifetime Limited
PS4B18	220-250V	13A	50/60 Hz	BS1363A (4)	1.8 m	280 x 52 x 26	0.4 kg	-	-	Lifetime Limited
PS4B18USBW	220-250V	13A	50/60 Hz	BS1363A (4)	1.8 m	339 x 52 x 26	0.4 kg	-	5V/2.4A	Lifetime Limited
PS6B18	220-250V	13A	50/60 Hz	BS1363A (6)	1.8 m	388 x 52 x 26	0.4 kg	-	-	Lifetime Limited
PS6B35W	220-250V	13A	50/60 Hz	BS1363A (6)	3 m	445 x 57 x 28	0.6 kg	-	-	Lifetime Limited

For more information, including pricing, specifications and availability, contact your local Tripp Lite Representative.

Daniel Weatherill

Channel Business Development Manager - United Kingdom
daniel_weatherill@triplite.com



Powering and Connecting Your World