



USB-C Hub with Laptop Stand

Powering and Connecting Your World

Bring Your Workstation Wherever You Go



The U460-ST4-4A-C USB-C hub keeps all your devices charged and connected without adding cable clutter.

Perfect for:

Connecting USB peripherals to a laptop for a fully functional computer workstation in a coffee shop, hotel or airport.

Tripp Lite's U460-ST4-4A-C four-port USB hub turns laptops into multi-port workstations. This lightweight hub doubles as a laptop stand that lets users adjust screen height for optimal comfort and ergonomics.

The hub's built-in plug connects to a compatible USB-C® or Thunderbolt™ 3 source laptop to deliver up to 20V 5A (100W) output, which is more than sufficient for charging and powering a MacBook®, Windows® laptop or Chromebook™. Its USB-A ports can support up to four peripheral devices like a memory card, mouse, smartphone and headset. The hub is an all-in-one tool for creating comfortable, clutter-free workspaces most anywhere.

Key Benefits

MULTI-DEVICE CONNECTIVITY

- Four USB-A ports connect computing peripherals to a laptop for control functions, file sharing, audio/video and other computing operations.

IMPROVED ERGONOMICS

- Five laptop angle options (from 15° to 36°) let users set the optimal position for comfortable viewing, recording and computer operation.
- Elevation can improve the attached device's heat dissipation.

ROBUST POWER DELIVERY

- USB-C PD 3.0 port supports 20V 5A (100W) power output for the host device.
- Fast Role Swap technology keeps data connections intact between source and peripherals when a power disconnection (such as AC charger unplugged from outlet) occurs.

AMPLE CHARGING

- 15W shared charging for four connected USB-A peripherals.
- One USB-A port also supports up to 1.5A charging.


HIGH-SPEED DATA TRANSFER

- USB 3.0 technology supports up to 5 Gbps data transfer speed between source and peripherals.

CONVENIENT OPERATION

- Hub connections reduce cable clutter
- Unfolds/folds quickly for immediate use/storage

Feature Focus



Model: U460-ST4-4A-C

A Multi-Device Connection

Four USB-A ports transmit data at up to 5 Gbps and share 15W maximum power.

B Fast Charging

One of the four USB-A ports supports up to 1.5A quick-charge technology.



C Adjustable View

Five angles, from 15° (2.8 in. raised) to 36° (5.5 in. raised), set optimal laptop position.

D PD 3.0 Charging

USB-C port connects to AC power source* for 100W power (85W for host laptop/15W for hub).



E Clutter-Free Workspace


Four clips beneath the hub keep the built-in USB-C cable organized.

F Secure Device Placement

Grooved anti-skid rubber base pads and rubber stand pads hold laptops in place.

G Folding Design

Hub folds into a compact unit for easy transportation.



Not Shown

Attached cable with USB-C plug delivers AC power to the connected source device.

SPECIFICATIONS



Ports	Data Transfer Technology / Rate	USB-C PD 3.0 Charging	USB-A Charging	External Power Supply Input	External Power Supply Output	External Power Supply Cord Length	Unit Dimensions (H x W x D)	Unit Weight	Limited Warranty
(x4) USB-A, (x1) USB-C	USB 3.0 / Up to 5 Gbps	Up to 20V/5A (100W) for Host Device	Up to 15W Shared; One Port Supports up to 1.5A	100–240V, 50/60 Hz, 1.5A	20V, 5A (100W)	4 ft. (1.2 m)	0.51 x 4.88 x 2.91 in. (1.3 x 12.4 x 7.4 cm)	0.4 lb. (0.17 kg)	One year

Learn more about Tripp Lite's full line of docks and hubs at triplite.com.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | triplite.com

*Requires user-supplied cable for connection to AC source.

© 2021 Tripp Lite. All trademarks are the property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.