



NEW PRODUCT ANNOUNCEMENT!

Rack & Cooling Solutions

SRDVRLB Security DVR Lockbox Enclosure



Secure Storage for Security Assets

Insurance companies and video surveillance best practices require security DVRs (digital video recorders) to be protected from theft, tampering and unauthorized access. Protecting security DVRs ensures the integrity of recordings and also prevents damage to substantial electronic hardware investments.

Tripp Lite's SRDVRLB security DVR lockbox enclosure provides a convenient all-in-one solution for storing and protecting DVRs. For use with both rack-mounted and non-rack-mounted DVRs, the enclosure mounts to a wall, table, counter or floor.





Key Features

- 5U enclosure mounts to a wall, table, counter or floor
- Locking steel cabinet prevents damage, theft, and tampering
- Works with both rack-mounted and non-rack-mounted DVRs
- Flow-through ventilation cools heat-sensitive equipment
- Top panel lifts off for quick and easy access to DVRs and cabling

The SRDVRLB is recommended for all locations that house security DVRs, including commercial/retail environments, offices, schools, public buildings, factories, restaurants, hotels, hospitals and residential properties.



Feature Focus



A Cooling Fan with Washable Air Filter

B Adjustable-Depth Rack-Mounting Rails (Include square mounting holes.)

C Lift-Off Top Panel

D Locking Front Door (Includes two keys.)

E Side Ventilation

F Rear-Panel Cable Access Ports (Also has two ports on bottom panel.)

G Rear-Panel Mounting Holes (Also has mounting holes on bottom panel.)

Not shown: Keys and rack equipment mounting hardware.

SPECIFICATIONS

MODEL: SRDVRLB

Rack Height	5U
Rack-Mounting Holes	Square
Maximum Installed Device Depth	16.25 in. (41.3 cm)
Unit Dimensions (H x W x D)	10 x 24.3 x 18.4 in. (25.4 x 61.7 x 46.7 cm)
Unit Weight	28.7 lb. (13 kg)
Material of Construction	Steel
Finish	Black powder-coat

Weight Capacity	60 lb (27.2 kg)
AC Input (For Fan)	120V, 50/60 Hz
AC Input Plug	NEMA 5-15P
AC Input Cord Length	3 ft. (0.9 m)
Standards	PCI-DSS, EIA/ECA-310-E, RoHS
Product Warranty	5-year limited warranty



Protect your valuable security equipment!

UPS Systems

- Rack and tower UPS systems provide reliable battery backup with surge and noise protection
- Models with voltage regulation, expandable runtime, pure sine wave output, network management, redundancy and energy-saving features are also available




Surge Protectors

- More than 150 models with up to 24 outlets provide surge and noise protection



Wall-Mount Rack Enclosure Cabinets

- Wall-mount rack enclosures from 5U to 26U provide locking, ventilated storage
- Keep rack-mounted equipment and other devices off the floor, out of the way and secure



Close-Coupled Cooling Solutions

- Portable and rack-mounted air conditioning units provide up to 24,000 BTU of cooling power
- Self-contained units do not require plumbing, floor drains or emptying water tanks



Learn more about Tripp Lite's full line of IT infrastructure solutions at www.triplite.com.

