## **Medical-Grade Power Strips** and Surge Protectors -**Now with Antimicrobial Protection!**



## Help Keep Patients, Staff Healthier

Tripp Lite's medical-grade power strips and surge protectors now have antimicrobial protection to help in the fight against healthcare-acquired infections (HAIs).

The incidence of HAIs is on the rise. The Centers for Disease Control and Prevention (CDC) estimate nearly two million hospital patients annually contract an HAI, at a cost of \$36 million a year.

These solutions include a patented coating designed to help reduce the risk of HAIs in hospitals and other medical environments. Any object in a healthcare setting frequently handled by staff, patients or visitors becomes a potential breeding ground for harmful microbes such as C. diff and MRSA. By adding an antimicrobial silver ionic powder coating to all power strips and surge protectors designed for healthcare use, Tripp Lite is helping medical staff reduce the transfer of dangerous microbes. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

## Key Features of Tripp Lite's Medical-Grade Power Strips and Surge Protectors

- Patented antimicrobial coating is 99.9 percent effective in inhibiting the growth of bacteria, viruses, mold and fungi on surfaces
- Meet Centers for Medicare and Medicaid Services (CMS) and Joint Commission regulations
- ULTRA models include patented fault protection for standalone use in patient-care vicinities

5	isobar		-	
1	Contract of the	1.1	11.1	1
4	-	1	4 4	
	8 5 1		Ga i	1
	TRIPP-LI	-	1.	
1				



	Nominal AC		Surge Protection		AC Input	AC Input
Model	Voltage/Amps	UL Compliance	Rating	AC Outlets	Cord Length	PlugType
OEM Series Power S	trips for Mobile Ap	oplication in Patient Care Vicini	ties (Specialty-Purpo	ose Relocatable Powe	r Strips)	
PS615HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	15 ft.	5-20P HG
PS607HG20AOEM	120V/20A	UL 1363A	n/a	6 (5-15/20R HG)	7 ft.	5-20P HG
PS-607-HG-OEM	120V/15A	UL 1363A	n/a	6 (5-15R HG)	7 ft.	5-15P HG
PS-415-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	15 ft.	5-15P HG
PS-407-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	7 ft.	5-15P HG
PS-402-HG-OEM	120V/15A	UL 1363A	n/a	4 (5-15R HG)	2 ft.	5-15P HG
PS-410-HGOEMCC	120V/15A	UL 1363A	n/a	4 (5-15R HG)	3 to 10 ft. (1)	5-15P HG
PS410HGOEMX	120V/15A	UL 1363A	n/a	4 (5-15R HG)	10 ft.	5-15P HG
Medical-Grade Powe	r Strips for Patien	t-Care Vicinities				
PS-406-HGULTRA	120V/15A	UL 60601-1 <sup>(2)</sup>	n/a	4 (5-15R HG)	6 ft.	5-15P HG
PS-415-HGULTRA	120V/15A	UL 60601-1 <sup>(2)</sup>	n/a	4 (5-15R HG)	15 ft.	5-15P HG
SPS415HGULTRA	120V/15A	UL 60601-1 <sup>(2)</sup>	1,410 joules	4 (5-15R HG)	15 ft.	5-15P HG
Hospital-Grade Powe	er Strips (For Use (	Outside Patient-Care Vicinities	Only)			
PS-615-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	15 ft.	5-15P HG
PS-606-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	6 ft.	5-15P HG
PS-602-HG	120V/15A	UL 1363	n/a	6 (5-15R HG)	1.5 ft.	5-15P HG
PS-415-HG	120V/15A	UL 1363	n/a	4 (5-15R HG)	15 ft.	5-15P HG
Hospital-Grade Surg	e Protectors (For L	Jse Outside Patient-Care Vicinit	ties Only)			
SPS-615-HG	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	15 ft.	5-15P HG
SPS610HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	10 ft.	5-15P HG (Right Angle)
SPS606HGRA	120V/15A	UL 1363 & UL 1449 (4th Ed.)	1,050 joules	6 (5-15R HG)	6 ft.	5-15P HG (Right Angle)

ord. (2) Meets the standards of a medical device when installed properly







## **Specifications**