



Eaton's Tripp Lite series BC36ML home network battery backup

Keep working through power problems with a UPS system built for home networks. This compact UPS powers Internet gateways, IP cameras, VoIP phones and other home office essentials.



Designed to keep you connected

- Keep critical connected equipment running for up to five hours or more during a power outage.
- Maintain your ability to remotely control your connected devices with no loss of power.
- Safeguard connected devices with built-in overcurrent protection.

Adaptable

- Choose from four output voltages as well as four output connector types (see p.2) to be compatible with any critical application power needs.

Simple

- Identify output voltage and battery capacity from user-friendly LEDs.
- Use the home network battery backup as a mini battery bank with its cold-start function.

Compact and silent



- Replace the manufacturer-provided power supplies tied to your devices to cut down on clutter.
- Enjoy the silent, stylish power protection offered by the home network battery backup.

EATON


Powering Business Worldwide

Eaton's Tripp Lite series home network battery backup


BARREL ADAPTERS INCLUDED:



- ① On/Off button
- ② Four LEDs indicate output voltage setting or remaining battery life.
- ③ C6 inlet for the detachable input power cord.
- ④ 3 ft. detachable output cord with 4 connector options.



TYPICAL RUNTIMES:



SPECIFICATIONS:

	BC36ML
AC input voltage	100-240V AC
AC input plug type / cord length	NEMA 5-15P / 3 ft. (0.9 m)
Input frequency	50/60 Hz
Output voltage / Amps	9V/3A; 12V/3A; 15V/2.4A; 19V/1.89A
Output connection barrel adapters	5.5 x 2.5 mm; 5.5 x 2.1 mm; 4.75 x 1.7 mm; 3.5 x 1.35 mm
Power rating	36W
Battery type	Li-ion x2 (ICR18650)* Cell weight: 45g Max
Battery capacity	3.7V / 2200mAh quantity 2
Dimensions (H x W x D)	1.2 x 3.8 x 5.4 in. (30 x 96 x 136 mm)
Weight	0.8 lb. (0.4 kg)
Operating temperature	32° to 95° F (0° to 35° C)
Certifications	UL 62368-1, TUVus, FCC Class B
Warranty	2-year limited

* Typical full-charge time (may vary): ~4 hours

For more information, visit
tripp-lite.eaton.com/mini-ups

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

© 2023 Eaton
 All Rights Reserved
 Printed in USA
 BR153172EN / 23-07-767
 August 2023



Eaton is a registered trademark.
 All other trademarks are property
 of their respective owners.

Follow us on social media to get the
 latest product and support information.

