TRIPP LITE USB-C QUICK REFERENCE GUIDE

VIDEO CABLES

Transfer data and video over a single cable, backward compatible with previous versions of USB.

- Models include USB-C to HDMI, DisplayPort, DVI and VGA with resolutions up to 4K
- Most models support DP Alt Mode to allow a compatible device to output HD or UHD via USB-C
- Fumble-free reversible USB-C plug connects in either direction for a quick connection every time



| Model | Color | Length (ft.) | In-Line Adapter | Bi- Directional | HDR | HDCP Version | HDMI | mDP | DP | DVI | VGA | Locking Connector |
|-----------------|-------|--------------|--------------------|--------------------|----------|-----------------|------|------|------|-------|-------------|----------------------|
| U444-003-H | Black | 3 | √ √ | Directional | Hon | 1.4 | 4K30 | mer | | 5 | VOA | Connector |
| U444-003-H4K6BM | Black | 3 | √ | | | 2.2 | 4K60 | | | | | |
| U444-003-H4K6BE | Black | 3 | - | | | 2.2 | 4K60 | | | | | |
| U444-003-H4K6WE | White | 3 | | | | 2.2 | 4K60 | | | | | |
| U444-006-H | Black | 6 | √ | | | 1.4 | 4K30 | | | | | |
| U444-006-H4K6BM | Black | 6 | √ | | | 2.2 | 4K60 | | | | | |
| U444-006-H4K6BE | Black | 6 | | | | 2.2 | 4K60 | | | | | |
| U444-006-H4K6WE | White | 6 | | | | 2.2 | 4K60 | | | | | |
| U444-009-H4K6BE | Black | 9 | | | | 2.2 | 4K60 | | | | | |
| U444-009-H4K6WE | White | 9 | | | | 2.2 | 4K60 | | | | | |
| U444-010-H4K6BM | Black | 10 | √ | | | 2.2 | 4K60 | | | | | |
| U444-015-H4K6BM | Black | 15 | √ | | | 2.2 | 4K60 | | | | | |
| U444-016-H | Black | 16 | √ | | | 1.4 | 4K30 | | | | | |
| U444-006-MDP | Black | 6 | ✓ | | ✓ | 1.3 | | 4K60 | | | | |
| U444-003-DP-BD | Black | 3 | | √ | √ | 2.2 | | | 4K60 | | | ✓ |
| U444-003-DP-BE | Black | 3 | | | ✓ | 2.2 | | | 4K60 | | | ✓ |
| U444-003-DP | Black | 3 | √ | | ✓ | 1.3 | | | 4K60 | | | √ |
| U444-006-DP-BE | Black | 6 | | | √ | 2.2 | | | 4K60 | | | ✓ |
| U444-006-DP | Black | 6 | ✓ | ✓ | ✓ | 1.3 | | | 4K60 | | | ✓ |
| U444-006-DP-BD | Black | 6 | ✓ | ✓ | ✓ | 2.2 | | | 4K60 | | | ✓ |
| U444-010-DP | Black | 10 | | | ✓ | 1.3 | | | 4K60 | | | √ |
| U444-010-DP-BD | Black | 10 | ✓ | ✓ | ✓ | 2.2 | | | 4K60 | | | ✓ |
| U444-003-V | Black | 3 | ✓ | | | | | | | | 1920 x 1200 | |
| U444-006-V | Black | 6 | ✓ | | | | | | | | 1920 x 1200 | |
| U444-016-V | Black | 16 | ✓ | | | | | | | | 1920 x 1200 | |
| U444-003-D | Black | 3 | ✓ | | | 1.3 | | | | 1080p | | |
| U444-006-D | Black | 6 | ✓ | | | 1.3 | | | | 1080p | | |
| U444-010-DE | Black | 10 | | | | 1.3 | | | | 1080p | | |
| U444-016-D | Black | 16 | ✓ | | | 1.3 | | | | 1080p | | |



For more information, contact:

Tripp Lite Pre-Sales Support 773.869.1236 | solutions@tripplite.com

