



## NEW PRODUCT ANNOUNCEMENT!

### Panel Mount Solutions

# Universal Panel Mount & Keystone Jack Products Customize Installations

## Organize & Manage All Types of Connections

Universal patch panels feature blank cutouts compatible with virtually every type of keystone jack or snap-in coupler. Each patch panel mounts easily into 1U or 2U of any EIA-standard 19-inch wide rack or enclosure.



- Accommodates all keystone jacks, including RJ45 Ethernet, HDMI, USB, DisplayPort/Mini DisplayPort, audio/video, and voice
- Ports are numbered for easy connection identification
- Choose 12, 16, 24 or 32 ports
- Also available: N062-024-KJ-SH rack-mount 24-port shielded panel with grounding wire and rear cable manager to keep cabling neat and organized

## Limitless Combinations of Connections

Keystone jacks and snap-in couplers allow you to customize a patch panel or wallplate with any combination of connections that suits your installation.

These simple solutions add versatility with virtually millions of combinations of jacks and couplers – configure your installation in the most efficient and organized way to reduce cable clutter, color-code connections and put ports where you need them.

## One Universal Patch Panel...



Model: N062-024-KJ-SH

## Manages All These Connections



RJ45 Ethernet



Shielded



HDMI



USB



DisplayPort/  
Mini DP



Audio/Video

## Mount a Port Virtually Anywhere



All-in-one keystone jacks with panel-mount adapters allow mounting to a fixed location, such as a podium, kiosk or wall panel.

See Reverse for Tripp Lite Keystone Panels, Jacks and Cable Solutions

# Tripp Lite Keystone Panels, Jacks and Cable Solutions

## BLANK KEYSTONE JACK PANELS

Model Number	Description	Model Number	Description
N062-012-KJ	1U, 12-Port Unshielded	N062-024-KJ-SH	1U, 24-Port Shielded
N062-016-KJ	1U, 16-Port Unshielded	N062-032-KJ	2U, 32-Port Unshielded
N062-024-KJ	2U, 24-Port Unshielded		

## CAT6/6A KEYSTONE JACKS

### Cat6/6a RJ45 Couplers

Model Number	Description	Color	Model Number	Description	Color
N235-001	Cat6 Straight-Through RJ45 Coupler (F/F)	Black	N235-001-6A	Cat6a Straight-Through RJ45 Coupler (F/F)	White
N235-001-WH	Cat6 Straight-Through RJ45 Coupler (F/F)	White	N235-001-WH-6AD	Cat6a Straight-Through RJ45 Coupler w/Down-Angled Port (F/F)	White
N235-001-SH	Cat6 Straight-Through Shielded RJ45 Coupler (F/F)	Silver	N235-001-SH-6A	Cat6a Straight-Through Shielded RJ45 Coupler (F/F)	Silver
N235-001-SH-D	Cat6 Straight-Through Shielded RJ45 Coupler w/Down-Angled Port (F/F)	Silver	N235-001-SH-6AD	Cat6a Straight-Through Shielded RJ45 Coupler w/Down-Angled Port (F/F)	Silver

### Cat6/6a 110-Style RJ45 Jacks

Model Number	Description	Color	Model Number	Description	Color
N238-001-WH-TF	Cat6 Toolless RJ45 Jack	White	N238-001-WH	Cat6 110-Style Punch-Down RJ45 Jack	White
N238-001-GY-TFA	Cat6a Toolless RJ45 Jack	Gray	N238-001-YW	Cat6 110-Style Punch-Down RJ45 Jack	Yellow
N238-001-SH-TFA	Cat6a Toolless Shielded RJ45 Jack	Gray	N238-010-BK	Cat6 110-Style Punch-Down RJ45 Jack, 10 pack	Black
N238-001-BL	Cat6 110-Style Punch-Down RJ45 Jack	Blue	N238-025-BL	Cat6 110-Style Punch-Down RJ45 Jack, 25 pack	Blue
N238-001-GN	Cat6 110-Style Punch-Down RJ45 Jack	Green	N238-025-RD	Cat6 110-Style Punch-Down RJ45 Jack, 25 pack	Red
N238-001-RD	Cat6 110-Style Punch-Down RJ45 Jack	Red	N238-025-WH	Cat6 110-Style Punch-Down RJ45 Jack, 25 pack	White

## CAT6A HDBASET RJ45 CONNECTOR

Model Number	Description	Color	Model Number	Description	Color
BHDBT-001-FF	Cat6a Straight-Through RJ45 Coupler for HDBaseT (F/F)	White	BHDBT-001-KJ-GY	Cat6a Toolless RJ45 Jack for HDBaseT	Gray

## CAT6A CABLE BUNDLES

Model Number	Description	Color	Model Number	Description	Color
N261-006-6MM-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/M), 6 ft.	Blue	N261-015-6MF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/F), 15 ft.	Blue
N261-010-6MM-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/M), 10 ft.	Blue	N261-006-6FF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (F/F), 6 ft.	Blue
N261-015-6MM-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/M), 15 ft.	Blue	N261-010-6FF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (F/F), 10 ft.	Blue
N261-006-6MF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/F), 6 ft.	Blue	N261-015-6FF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (F/F), 15 ft.	Blue
N261-010-6MF-BL	Cat6a Pre-Terminated Bundle, (6x) RJ45 (M/F), 10 ft.	Blue			

## HDMI KEYSTONE/PANEL-MOUNT COUPLERS

Model Number	Description	Color	Model Number	Description	Color
P164-000-KJ-WH	HDMI Wallplate Coupler (F/F)	White	P164-000-KP-BK	HDMI Panel-Mount Coupler (F/F)	Black
P164-000-KPA-BK	HDMI Panel-Mount Coupler w/Angled Connector (F/F)	Black			

## HDMI KEYSTONE/PANEL-MOUNT CABLES

Model Number	Description	Color	Model Number	Description	Color
P162-001-KPA-BK	High-Speed HDMI + Ethernet Panel-Mount Extension Cable w/Angled Connector (M/F), 1 ft.	Black	P164-001-KPA-BK	High-Speed HDMI + Ethernet Panel-Mount Cable w/Angled Connector (F/F), 1 ft.	Black

## USB-A KEYSTONE/PANEL-MOUNT COUPLERS

Model Number	Description	Color	Model Number	Description	Color
U060-000-KP-BK	USB 2.0 Panel-Mount Coupler (F/F)	Black	U325-000-KP-BK	USB 3.0 Panel-Mount Coupler (F/F)	Black
U060-000-KPA-BK	USB 2.0 Panel-Mount Coupler w/Angled Connector (F/F)	Black	U325-000-KPA-BK	USB 3.0 Panel-Mount Coupler w/Angled Connector (F/F)	Black

## USB-A KEYSTONE/PANEL-MOUNT CABLES

Model Number	Description	Color	Model Number	Description	Color
U024-001-KPA-BK	USB 2.0 Panel-Mount Ext. Cable, Angled Connector (M/F), 1 ft.	Black	U325-001-KPA-BK	USB 3.0 Panel-Mount Coupler Cable w/Angled Connector (F/F), 1 ft.	Black
U060-001-KPA-BK	USB 2.0 Panel-Mount Coupler Cable, Angled Connector (F/F), 1 ft.	Black	U324-003-KJ	USB 3.0 Keystone Jack Extension Cable (M/F), 3 ft.	Blue
U324-001-KPA-BK	USB 3.0 Panel-Mount Ext. Cable, Angled Connector (M/F), 1 ft.	Black			

## MINI DISPLAYPORT TO DISPLAYPORT KEYSTONE/PANEL-MOUNT CONNECTOR & CABLE

Model Number	Description	Color	Model Number	Description	Color
P169-000-KPA-BK	mDP to DisplayPort Panel-Mount Adapter w/Angled Connector (F/F)	Black	P169-001-KPA-BK	mDP to DisplayPort Panel-Mount Adapter Cable w/Angled Connector (F/F), 1 ft.	Black

## COMPONENT/RCA AUDIO/VIDEO KITS

Model Number	Description	Model Number	Description
A008-000-KJ	3-Piece Component Video Kit (R, G, B)	A050-000-KJ	2-Piece RCA Stereo Audio Kit (R, W)
A020-000-KJ	3-Piece Composite Audio/Video Kit (R, Y, W)	A050-000-ST-KJ	2-Piece RCA Stereo Audio to Screw Terminal Kit (R, W)

## COAXIAL KEYSTONE/PANEL-MOUNT COUPLER

Model Number	Description
A230-001-KP	BNC Coaxial All-in-One Coupler, 75 Ohms

See Tripp Lite's full line of universal patch panels and accessories at [www.triplite.com](http://www.triplite.com)

