

### Safe-IT™ Surge Protectors

Powering and Connecting Your World

## Add Power Protection and Germ Resistance to Your Workspace



Safe-IT surge protectors declutter workspaces and help reduce exposure to germs.

#### Perfect for:

Shared work/learn spaces like schools, offices, coffee shops and libraries.

Tripp Lite's new surge protectors with antimicrobial properties provide safe power and charging for multiple devices while also helping to protect against germs. These additions to the Safe-IT product collection feature an antimicrobial housing that aids in resisting the growth of bacteria, viruses, fungi, mold and mildew.

Safe-IT surge protectors come in direct plug-in, strip and clamp designs, as well as spherical, circular and cube-shaped models. These products provide up to 2100 joules of protection against power surges and up to six USB charging ports to keep devices powered and workspaces organized.

#### **Key Benefits**

#### **RELIABLE SURGE PROTECTION**

- Surge-protected NEMA 5-15R outlets distribute power to multiple devices using only one AC wall outlet.
- LEDs show protected status at a glance.
- On/off switch offers one-touch control (select models).

#### **POWERFUL USB CHARGING**

- USB-A and USB-C ports provide up to 7.8A of power for charging mobile devices (ports and amps vary by model).
- USB ports eliminate the need for AC adapters for charging cords, leaving outlets available for AC devices.

#### **ANTIMICROBIAL PROTECTION**

- Additives in the plastic resin give the housings antimicrobial properties.
- Antimicrobial protection aids in resisting the growth of bacteria, viruses, fungi, mold and mildew.
- Safe-IT products minimize the presence of germs to provide a safer, cleaner and healthier work environment.

#### **VERSATILE FORM FACTORS**

#### **Direct Plug-in Models**

- Direct plug-in design reduces cable clutter.
- SK5BUCAM has outlets that rotate 90° for easier plug connection.

#### **Sphere & Cube Models**

- Outlets and ports power up to 9 devices in all directions for convenient use in meetings.
- TLP368CUBEUAM surge protector cube includes a detachable USB wall charger.
- TLP410UCUFOAM conference room surge protector supports connection of a smart speaker.

#### **Strip & Clamp Models**

- Form factors allow unobtrusive placement on or around work desks.
- TLP608DMUAM and TLP610BUAM strips models include an input power cord with a braided jacket for flexible positioning and better durability during everyday use.
- Retractable USB charger and permanent mounting options are available.

#### **Feature Focus**

#### **A** Power Distribution

Surge-protected NEMA 5-15R outlets distribute power to up to 6 devices.

#### **B** USB Charging

USB-A and USB-C ports charge and power up to 6 devices.

#### © Powerful Surge Protection

Up to 2100-joule surge protection with LED verification.

#### Rocker Switch

On/Off switch offers one-touch control (select models).

#### **Antimicrobial Housing**

Additives in the plastic resin give the housings antimicrobial properties.



#### **DIRECT PLUG-IN MODELS**



Model: SK3BUAM Model: SK5BUCAM

# INTERNATIONAL TRAVELER? The SK2UTRAVAM charger with antimicrobial protection includes 5 plug options for worldwide compatibility.\* \* Model does not have surge-protected outlets.






SPHERE and CUBE MODELS

Circular Model: TLP410UCUFOAM



Model: TLP368CUBEUAM





Model: TLP648UCBAM

#### **SPECIFICATIONS**

ST ECH TOATIONS (RoHS									
		AC	Outlet	Surge Protection	USB Ports/	Cord	Housing Dimensions	Unit	Ultimate Lifetime
Model	Form Factor	Voltage	Qty.	(Joules)	Total Amps	Length	(H x W x D)	Weight	Insurance
SK3BUAM	Direct Plug-In	120V	3	1050	2 USB-A/2.4A		2.4 x 1.3 x 3.2 in.	0.3 lb.	\$5,000
							(61 x 33 x 81 mm)	(0.13 kg)	
SK5BUCAM	Direct Plug-In	120V	5 (4	1050	1 USB-A,	<u> </u>	4.9 x 4.7 x 1.5 in.	0.7 lb.	\$25,000
			rotatable)		1 USB-C/3.9A		(124 x 119 x 38 mm)	(0.32 kg)	
TLP38UAM	Sphere	120V	3	540	4 USB-A/4.8A	8 ft.	3.6 x 3.6 x 3.3 in.	1.3 lb.	\$10,000
						(2.4 m)	(91 x 91 x 84 mm)	(0.6 kg)	
TLP368CUBEUAM	Cube w/Detachable	120V	3	540	6 USB-A/7.2A	8 ft.	3.6 x 3.6 x 3.3 in.	1.2 lb.	\$50,000
	USB Wall Charger					(2.4 m)	(91 x 91 x 84 mm)	(0.5 kg)	
TLP410UCUFOAM	Circle	120V	4	1080	3 USB-A/4.8A,	10 ft.	7.7 x 7.1 x 1.9 in.	1.9 lb.	\$100,000
			(rotatable)		1 USB-C/3A	(3 m)	(196 x 180 x 49 mm)	(0.86 kg)	
TLP608DMUAM	Clamp-Mount Strip	120V	6	2100	2 USB-A/2.4A	8 ft.	2.9 x 13.6 x 2.9 in.	1.5 lb.	\$40,000
						(2.4 m)	(73 x 345 x 73 mm)	(0.7 kg)	
TLP610BUAM	Strip	120V	6	990	2 USB-A/2.4A	10 ft.	13.1 x 1.3 x 1.9 in.	1.5 lb.	\$25,000
						(3 m)	(333 x 32 x 47 mm)	(0.7 kg)	
TLP648UCBAM	Desk Clamp	120V	6	1080	2 USB-A/4.8A,	8 ft.	5.2 x 2.7 x 5.3 in.	1.7 lb.	\$50,000
	· .				1 USB-C/3A	(2.4 m)	(132 x 69 x 135 mm)	(0.8 kg)	
TLP68UBAM	Strip w/Retractable	120V	6	1080	4 USB-A/3.4A	8 ft.	8.3 x 3.6 x 1.4 in.	1.8 lb.	\$50,000
	USB Charger					(2.4 m)	(210 x 92 x 36 mm)	(0.8 ka)	

All models come with a lifetime limited warranty.

Learn more about Tripp Lite's full line of surge protectors at tripplite.com.





