



Powering and Connecting Your World

NEW PRODUCT ANNOUNCEMENT

Wireless 4K HDMI Extender

Wirelessly Extend 4K HDMI Audio/Video Without Sacrificing Premium Signal Quality



Tripp Lite's new HDMI extender kit delivers a 4K audio/video wireless signal up to 98 ft. (30 m) from the source device with near-zero latency so you can enjoy full, rich picture and sound on a remote HDMI display. The kit's plug-and-play setup makes it easy to transmit crystal-clear content without a costly, obtrusive cable installation.

Key Benefits

WIRELESS SIGNAL TRANSMISSION

- Wireless transmission with a range of 98 ft. (30 m) saves space and installation costs associated with cabling.
- 60 GHz wireless frequency allows fast transmission and minimal interference from other wireless devices.

ZERO LATENCY

- 10.2 Gbps bandwidth transmits live audio and video with virtually no latency for a sharp viewing experience.

PREMIUM AUDIO/VIDEO


- Resolutions up to 3840 x 2160 @ 30 Hz provide UHD picture quality.
- 7.1-channel sound with DTS-HD and Dolby AC-3 digital audio support realistic video gaming and live televised events.

SIMPLE SETUP

- Plug-and-play setup allows you to connect the transmitter and receiver and start playing video right away, with no software or drivers required.
- Option to power transmitter and receiver units with a portable power source (laptop, power bank, etc.) via USB Micro-B port* skips the hassle of AC outlets that are out of reach.

* Requires USB Micro-B cable (sold separately), such as Tripp Lite's U050-010-GY-MAX USB-A to USB Micro-B cable.


Plug-and-Play Wireless 4K Transmission




Perfect for:

Live television events, digital signage, video conferencing and high-end gaming.

Feature Focus



Transmitter (Side View)



Receiver (Side View)

A Factory Reset Button

B Power LED

C Data Transmission LED

D USB Micro-B Power Input
(Cable Sold Separately)

E HDMI Input

F HDMI Output

G Power Input
(Power Supply Included)

SPECIFICATIONS

FC REACH



	Model: B127-1A1-WHD1
A/V Port	Transmitter: HDMI (Female); Input Receiver: HDMI (Female); Output
Max. Wireless 4K Transmission Distance	98 ft. (30 m)
Max. Resolution @ 30 Hz	3840 x 2160
Transmission Radio Frequency	60 GHz
Latency	Near-Zero
HDCP 2.2 Compatible	Yes
External Power Supply Input	100-240V~50/60 Hz, 0.2A
External Power Supply Output	5V / 1A
External AC Power Supply Plug Cord Length (Included)	NEMA 1-15P; 5 ft.
Alternate External Power Supply Port	USB Micro-B
Unit Dimensions (HxWxD)	3.11 x 2.13 x 2.29 in.
Unit Weight	0.26 lb.
Color	Black
Material of Construction	Aluminum
Limited Warranty	1 Year
Certifications	Tested to FCC, RoHS, REACH

Learn more about Tripp Lite's full line of extenders at tripplite.com.



Manufacturing Excellence



Tripp Lite Corporate Headquarters
1111 W. 35th Street, Chicago, IL 60609
773.869.1773 | tripplite.com