

3-Port Portable USB 3.0 SuperSpeed Hub with Keyboard/Mouse Sharing and File Transfer

MODEL NUMBER: **U360-003-KM**



Allows you to transfer files and share a single keyboard and mouse between two Windows PCs, Macs and/or OTG-compatible Android tablets and smartphones.

Description

The U360-003-KM 3-Port USB 3.0 SuperSpeed Hub does more than just connect USB peripherals to your computer. Built-in software allows you to share files and a single keyboard/mouse between devices:

- Two Windows personal computers (PC)
- Two Macs
- One PC and one Mac
- One PC and one Android tablet or smartphone
- One Mac and one Android tablet or smartphone

Just connect the built-in USB 3.0 cable to an available USB port on your Windows or Mac computer or laptop. Connect up to three USB devices, such as a flash drive or external hard drive, to the top ports. To transfer files from one device to another or share a keyboard and mouse with a second device, connect the included USB cable to the hub's SHARE port and an available USB port on another computer or On-the-Go (OTG) Android device. A USB Micro-B OTG adapter is included for connecting to Android tablets and smartphones.

The U360-003-KM supports USB 3.0 data transfer rates up to 5 Gbps—ten times faster than USB 2.0—and it's backward compatible with previous USB generations. Not only can you use one keyboard/mouse combination on two devices, you can also use the clipboard sharing feature to copy data from one computer and paste it in another.

The U360-003-KM receives power through its USB connection, so no external power supply is required. Its compact design fits easily into a purse, backpack, briefcase or laptop bag for quick connection anywhere.

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Copy and paste data between devices
- Compact design fits easily into laptop bag
- Share one keyboard/mouse between devices
- No external power supply required

System Requirements

- Windows 2000 SP3 and later (except 8 RT)
- Mac OS X 10.6 and later
- Android 2.2 and later with OTG compliance and Windroid Linker app
- Intel Pentium II or PowerPC G4 processor or higher
- 256MB RAM or higher
- 50MB hard drive space or higher
- USB 3.0 port needed to achieve USB 3.0 speeds

Package Includes

- U360-003-KM 3-Port USB 3.0 SuperSpeed Hub
- USB 2.0 Type-A cable (M/M), 4 ft.
- USB 2.0 Micro-B to Type-A (M/F) OTG adapter
- Owner's manual



Powering Business Worldwide



Features

Connects to Another Computer or On-the-Go (OTG) Android Device

- Share files between 2 electronic devices
- Share a keyboard and mouse between 2 electronic devices
- Share between 2 PCs, 2 Macs, PC and Mac, PC and OTG Android device, or Mac and OTG Android device
- Built-in software transfers files between devices
- Clipboard sharing for copy/paste between computers

Excellent Speed and Versatile Performance

- Connect up to 3 USB peripherals, such as flash drive or external hard drive
- Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0
- Backward compatible with previous USB generations
- Supports 11 languages— English, Spanish, French, German, Italian, Russian, Simplified Chinese, Traditional Chinese, Korean, Japanese, Portuguese

Take the Hub Anywhere

- Bus-powered through USB connection—no external power supply needed
- Compact design fits into purse, backpack, briefcase or laptop bag for travelling

Specifications

OVERVIEW	
UPC Code	037332190161
Product Type	Hub
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(3) USB A (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	16.22
Product Length (cm.)	41.2
Product Length (ft.)	1.35



Powering Business Worldwide



Product Length (m)	0.41
CONNECTIONS	
Number of Ports	3
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(3) USB 3.0 A (FEMALE)
Side B - Connector 2	USB 3.0 A (FEMALE)
PHYSICAL	
Color	Silver; White
Shipping Dimensions (hwd / in.)	1.20 x 6.70 x 3.90
Shipping Dimensions (hwd / cm)	3.05 x 17.02 x 9.91
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Packaging Type	Box
Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.