

Universal Phantom Manager - Distributed Cat5 KVM Switch

MODEL NUMBER: **0SU52015**



Description

- 1 Universal Phantom Manager (UPM) unit per system
- 1 Remote unit (Phantom Specter II USB or PS/2) per computer up to 63 per line

Features

- Single user control of up to 63 servers on a single line

Highlights

- Single user control of up to 63 servers on a single line
- Advanced OSD management and multi-layered security
- Pure hardware solution - BIOS level access
- Scalable - buy only what you need and add as you grow
- Flexible server/KVM console placement up to 110m/360ft away
- No external power supply at Specter units
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- DOS, Windows (3x, 9x, 2000, NT4, ME, XP and later), LINUX, UNIX, HP UX, QNX, SGI, FreeBSD, BeOS, Open VMS, Novell 3.12 - 6, SUN Solaris

Console

- VGA Monitor
- PS/2 Keyboard and Mouse

Resolution

- Supports video resolutions up to 1600 x 1200 @ 75Hz

Package Includes

- 0SU51011



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Advanced OSD management and multi-layered security
- Pure hardware solution - BIOS level access
- Scalable - buy only what you need and add as you grow
- Flexible server/KVM console placement up to 110m/360ft away
- No external power supply at Specter units
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

- 3 in 1 KVM Cable Kit
- RJ11 to DB9 Firmware Upgrade Cable
- Power Cord
- Owner's Manual

Specifications

OVERVIEW	
Users	1
Console	0
PHYSICAL	
Unit Dimensions (hwd / in.)	1.6 X 7.1 X 8
Unit Dimensions (hwd / cm)	4.15 X 18 X 20.4
Unit Weight (lbs.)	2.2
Unit Weight (kg)	1
Color	White
ENVIRONMENTAL	
Storage Temperature Range	-40 to 40 C (-40 to 104 F)
Operating Temperature	0 to 40 C (32 to 104 F)
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	1
CONNECTIONS	
Ports	1
PC/Server Connections	VGA; USB; PS/2
SPECIAL FEATURES	
Cat5 KVM Switch	1
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>