

Access IT Enterprise Centralized Remote Access Management

MODEL NUMBER: 0SU00019



Description

Solving the need to manage remote access

In today's complex corporate environments, IT managers are charged with managing remote server rooms and distributed IT assets at a "click's length," so that every problem is dealt with in real-time, or even better, prevented through ongoing maintenance. This calls for a secure, simple, yet cost-effective solution to manage today's ever-growing list of remote access connections and protocols.

Enhancing the level of IT service

AccessIT is a secure web-based, centralized remote access management solution that enhances IT efficiency and productivity. AccessIT consolidates all remote access services into a single session, providing IT staff with critical on-demand remote access to all IT assets, regardless of their physical location.

AccessIT is targeted at mid-sized organizations, allowing for the connection of up to 250 targets, and providing access to up to 10 IT personnel that are in charge of the daily management, maintenance, monitoring and control of the company's mission critical IT assets. AccessIT Enterprise Edition is designed for larger organizations, and supports up to 1000 targets, and more than 20 users.

Providing the Real Needs of IT

Its unique, open platform architecture provides a single portal to access and control ALL IT hardware (servers, console servers, PDUs, etc.) regardless of manufacturer. By embracing IT products from a wide range of vendors, AccessIT enables organizations to leverage their existing IT equipment, knowledge, and training.

Highlights

- AccessIT Enterprise allows for the connection of up to 1000 targets, and provides access to 20 or more users
- Integrates in-band and out-of-band access
- Combines access and power
- Manages access and control of heterogeneous environments
- Maximizes tools that have already been deployed
- Overcomes implementation challenges
- Increases operational efficiency while maintaining security
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- AccessIT Enterprise Manager Appliance
- Rackmount kit

Features

- AccessIT Enterprise allows for the connection of up to 1000 targets, and provides access to 20 or more users
- Integrates in-band and out-of-band access
- Combines access and power
- Manages access & control of heterogeneous environments
- Maximizes tools that have already been deployed
- Overcomes implementation challenges
- Increases operational efficiency while maintaining security
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	654518212525
Accessory Type	Remote Management
Accessory Class	KVM Switch Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	10.00 x 23.60 x 33.50
Shipping Dimensions (hwd / cm)	25.40 x 59.94 x 85.09
Shipping Weight (lbs.)	39.90
Shipping Weight (kg)	18.10
Unit Dimensions (hwd / in.)	1.700 x 16.800 x 26.800
Unit Dimensions (hwd / cm)	4.32 x 42.62 x 67.95
Unit Weight (lbs.)	34.8
Unit Weight (kg)	15.79
ENVIRONMENTAL	
Storage Temperature Range	-20 to 80 C
Relative Humidity	5 to 95%, Non-Condensing
Operating Temperature	0 to 40 C
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.