

Smart 116 - 16-Port Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22082



Description

Save Space and Money

From SOHO to Enterprise

Features

- 16 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- 16 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- DOS, Windows, LINUX, UNIX, MAC and all other major operating systems

Console

- VGA Monitor
- PS/2 Keyboard and Mouse

Resolution

- Supports video resolutions up to 1600 x 1200 @ 75Hz

Package Includes

- Smart 116
- RS232 Cable
- Power Cord
- Rackmount Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	654518209495
Console	No
CONNECTIONS	
Number of Ports	16



Powering Business Worldwide



PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.70 x 5.90 x 10.20
Shipping Dimensions (hwd / cm)	11.94 x 14.99 x 25.91
Shipping Weight (lbs.)	4.10
Shipping Weight (kg)	1.86
Unit Dimensions (hwd / in.)	1.600 x 8.500 x 4.800
Unit Dimensions (hwd / cm)	4.15 x 21.5 x 12.2
Unit Weight (lbs.)	2.2
Unit Weight (kg)	1.00
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Relative Humidity	80% Non-Condensing
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.