

1U Rack-Mount Console with 17-in. LCD

MODEL NUMBER: 0SU52088



Description

The 0SU52088 1U Rackmount Console features an integrated 17" LCD panel, keyboard, and touch pad, all in a 1U rackmountable housing. It connects to both PS/2 and USB computers/KVM switches (Use a B015-000 PS/2 to USB adapter to connect via USB). Constructed of heavy-duty steel housing. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Space savings with 1U rack-mount drawer design
- Features 17-inch LCD panel
- Supports resolutions of up to 1280 x 1024
- Connects to PS/2 or USB computers/KVM switches (Use a B015-000 PS/2 to USB adapter to connect via USB)
- Constructed of heavy-duty steel housing
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Control an entire network in just 1U of rack space; includes keyboard, 17" LCD screen, and touch pad
- Connects to PS/2 or USB computers/KVM switches (Use a B015-000 PS/2 to USB adapter to connect via USB)
- Supports video resolutions up to 1280 x 1024
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Computer or KVM with a VGA monitor port and USB or PS/2 keyboard/mouse ports

Package Includes

- 0SU52088 1U Rackmount Console
- PS/2 KVM Cable Kit
- Mounting hardware
- Key for front panel lock
- Power Cord
- User Manual

Specifications

OVERVIEW	
UPC Code	654518211191
Technology	PS/2; VGA/SVGA
CONNECTIONS	
Number of Ports	0
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	



Powering Business Worldwide



Color	Black
Shipping Dimensions (hwd / in.)	8.07 x 22.05 x 29.53
Shipping Dimensions (hwd / cm)	20.50 x 56.01 x 75.01
Shipping Weight (lbs.)	39.68
Shipping Weight (kg)	18.00
COMMUNICATIONS	
IP Remote Access	No
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.