

PS/2 to USB Converter

MODEL NUMBER: 0DT60002



Description

Preserve Your IT investments

Keep your PS/2 legacy equipment! The PS/2 to USB Converter, a small, plug & play converter, transforms PS/2 equipment from outdated devices to valuable tools for today's data centers.

Rather than advocate "rip and replace" IT solutions, this adapter preserves past investments by repurposing and updating existing IT equipment. Once you have gone through the hassle of setting up a KVM switch, for example, it is inconvenient and expensive to throw it out and start from scratch. With the PS/2 to USB Converter, your life at the rack only gets easier: you can now use your KVM switch with a new generation USB keyboard and mouse. With your PS/2 KVM switches, you can still extend the life of the IT equipment that you already bought.

Flexible USB Support

With the PS/2 to USB Converter, you can use your PS/2 device (KVM switches, KVM extenders, and servers) with a USB keyboard and mouse.

Unlike other converters, the PS/2 to USB Converter accommodates multiple permutations of keyboard and mice combinations:

- Supports USB keyboard with USB mouse
- Supports USB keyboard with PS/2 mouse
- Supports USB mouse with PS/2 keyboard

Features

- Compatible with PS/2 servers / KVM switches / KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Compatible with PS/2 servers/KVM switches/KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- PS/2 Computer / KVM Switch / KVM Extender
- USB and/or PS/2 keyboard and mouse
- Compatible with most keyboards; supports 104 keys only

Package Includes

- PS/2 to USB Converter

Specifications

OVERVIEW	
UPC Code	654518212235



Powering Business Worldwide



Accessory Type	Serial Adapter
Technology	PS/2
Accessory Class	KVM Switch Accessories
INPUT	
Product Length (in.)	11.4
CONNECTIONS	
Side A - Connector 1	(2) MINI DIN-6 (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
PHYSICAL	
Color	Black
Material of Construction	ABS
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5mm
Shipping Dimensions (hwd / in.)	5.50 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.97 x 9.91 x 1.27
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	41° to 104°F (5° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	0% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.