

## PS/2 to USB Converter

MODEL NUMBER: 0DT60002



### Description

Preserve Your IT investments

### Flexible USB Support

- Supports USB keyboard with USB mouse
- Supports USB keyboard with PS/2 mouse
- Supports USB mouse with PS/2 keyboard

### Features

- Compatible with PS/2 servers / KVM switches / KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

### Highlights

- Compatible with PS/2 servers/KVM switches/KVM extenders
- Pure hardware solution - no software/network conflicts
- No need for external power
- Compact size
- Plug & play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### System Requirements

- PS/2 Computer / KVM Switch / KVM Extender
- USB and/or PS/2 keyboard and mouse
- Compatible with most keyboards; supports 104 keys only

### Package Includes

- PS/2 to USB Converter



<b>OVERVIEW</b>	
UPC Code	654518212235
<b>INPUT</b>	
Product Length (in.)	11.4
<b>PHYSICAL</b>	
Wire Gauge (AWG)	28
Shipping Dimensions (hwd / in.)	5.50 x 3.90 x 0.50
Shipping Dimensions (hwd / cm)	13.97 x 9.91 x 1.27
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
Unit Packaging Type	Polybag
Material of Construction	ABS
Color	Black
Cable Outer Diameter (OD)	3.5mm
Cable Jacket Rating	VW-1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	41 to 104 F (5 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0% to 80% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	(2) MINI DIN-6 (MALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 1.1 (up to 12 Mbps)
Technology	PS/2; USB
<b>CERTIFICATIONS</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>